CU Compressed 15kV NLEPR Insulation 100% IL AIA Red PVC Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Three Conductor Copper, 175 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level, Tape Shield, Aluminum Interlocked Armor (AIA), Polyvinyl Chloride (PVC) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 175 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
7. **Filler:** Wax paper filler
8. **Binder:** Polypropylene tape
9. **Armor:** Aluminum Interlocked Armor (AIA)
10. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 15KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend when UL listed. Rated at -40°C for cold bend and cold impact and marked with "LTGG" when CSA listed or dual UL/CSA listed. For uses in Class I and II, Division 2 hazardous locations per NEC Article 501 and 502.Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

SOUTHWIRE [SYMBOL - LIGHTING BOLT] #P# (UL) 3/C [#AWG or #kcmil] CU 175 MILS NL-EPR AIA 15KV 100% INS LEVEL 25% TS MV-105 FOR CT USE SUN. RES. FOR DIRECT BURIAL FT4 YEAR (NESC) [SEQUENTIAL FEET MARKS]

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Ground	Diameter Over armor	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size
	AWG/ Kcmil	No. of Strands	inch	inch	inch	No. x AWG	inch	mil	inch	lb/ 1000ft	lb/ 1000ft	lb	inch	inch
TBA	2	7	0.283	0.671	0.731	1x6	1.912	60	2.032	886	2063	1592	14.2	2.5
TBA	1	19	0.322	0.71	0.77	1x4	1.996	60	2.116	1104	2356	2008	14.8	2.5
556860	1/0	19	0.362	0.75	0.81	1x4	2.192	60	2.241	1324	2745	2534	15.7	3
TBA	2/0	19	0.405	0.793	0.853	1x4	2.175	60	2.295	1588	2999	3194	16.1	3
TBA	3/0	19	0.456	0.844	0.904	1x3	2.286	75	2.436	1959	3533	4027	17.1	3
TBA	4/0	19	0.512	0.9	0.96	1x3	2.407	75	2.557	2382	4066	5078	17.9	3.5
TBA	250	37	0.558	0.954	1.014	1x2	2.523	75	2.673	2798	4602	6000	18.7	3.5
TBA	350	37	0.661	1.057	1.117	1x2	2.746	75	2.896	3760	5770	8400	20.3	3.5
556928	500	37	0.789	1.162	1.222	1x1	3.011	90	3.181	5253	7534	12000	22.3	4
TBA	750	61	0.968	1.374	1.434	1x1/0	3.43	90	3.61	7702	10470	18000	25.3	4.5

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.221	0.038	0.028	0.588+j0.502	0.221+j0.045	2296	150/160	165/185
1	0.128	0.175	0.035	0.026	0.544+j0.482	0.175+j0.043	2417	170/185	185/210
1/0	0.102	0.139	0.033	0.025	0.509+j0.463	0.139+j0.041	2541	195/210	215/240
2/0	0.082	0.112	0.03	0.023	0.483+j0.444	0.112+j0.040	2674	220/235	245/275
3/0	0.064	0.087	0.028	0.022	0.458+j0.423	0.087+j0.038	2832	250/270	285/315
4/0	0.051	0.07	0.026	0.02	0.440+j0.401	0.070+j0.037	3005	285/305	325/360
250	0.043	0.059	0.024	0.02	0.427+j0.381	0.059+j0.036	3173	310/335	360/400
350	0.031	0.043	0.021	0.018	0.406+j0.346	0.043+j0.034	3492	375/400	435/490
500	0.021	0.03	0.017	0.016	0.386+j0.315	0.030+j0.032	3817	450/485	535/600
750	0.014	0.021	0.015	0.015	0.361+j0.263	0.021+j0.031	4474	545/585	670/745

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

* NEC ampacities are based on:
* For Duct: Table 310.60(C)(13) Detail 1.
* For Free Air: Table 310.60(C)(5).
* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.
* Capacitive Reactance is between Phase-to-Shield.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved