



CU Compressed 25kV NLEPR Insulation 133% IL AIA Orange PVC Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Three Conductor Copper, 320 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, Aluminum Interlocked Armor (AIA), Polyvinyl Chloride (PVC) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 320 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
7. **Filler:** Wax paper filler
8. **Binder:** Polypropylene tape
9. **Armor:** Aluminum Interlocked Armor (AIA)
10. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 25KV AIA cables are armored cables for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501, 502, and 503.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B496 Compact Round Concentric-lay-standard copper
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test





- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

SOUTHWIRE [SYMBOL - LIGHTING BOLT] ## AIA (UL) 3/C [#AWG or #kcmil] CU 320 MILS NL-EPR 25KV 133% INS LEVEL 25% TS MV-105 FOR CT USE SUN. RES. FOR DIRECT BURIAL FT4 YEAR (NESC) [SEQUENTIAL FEET MARKS]

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Ground	Diameter Over armor	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius
	AWG/Kcmil	No. of Strands	inch	inch	inch	No. x AWG	inch	mil	inch	lb/1000ft	lb/1000ft	lb	inch
TBA	1	19	0.322	1.000	1.060	1x4	2.654	75	2.804	974	3482	2008	19.6
671717	1/0	19	0.361	1.040	1.100	1x4	2.747	80	2.907	1386	3949	2534	20.3
TBA	2/0	19	0.405	1.083	1.143	1x4	2.834	75	2.984	1440	4214	3194	20.8
TBA	3/0	19	0.456	1.134	1.194	1x3	2.944	75	3.094	1802	4741	4027	21.6
TBA	4/0	19	0.512	1.190	1.250	1x3	3.065	90	3.245	2214	5431	5078	22.7
TBA	250	37	0.558	1.244	1.304	1x3	3.181	90	3.361	2577	5985	6000	23.5
139099	350	37	0.661	1.327	1.387	1x2	3.368	85	3.538	3814	7378	8400	24.8
668544	500	37	0.789	1.452	1.512	1x2/0	3.637	85	3.807	5453	9330	12000	26.6
TBA	750	61	0.968	1.664	1.724	1x1/0	4.089	90	4.269	7439	12333	18000	29.8

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1	0.128	0.162	0.059	0.050	0.487 + j0.511	0.128 + j0.042	3315	170/185	185/210
1/0	0.102	0.128	0.055	0.048	0.487 + j0.332	0.134 + j0.05	3435	195/210	215/240
2/0	0.081	0.102	0.051	0.046	0.486 + j0.525	0.128 + j0.042	3572	220/235	245/275
3/0	0.064	0.081	0.047	0.044	0.486 + j0.351	0.129 + j0.052	3730	250/270	285/315
4/0	0.051	0.065	0.044	0.043	0.486 + j0.351	0.129 + j0.052	3903	285/305	325/360
250	0.043	0.056	0.041	0.042	0.483 + j0.533	0.128 + j0.040	4071	310/335	360/400
350	0.031	0.041	0.037	0.039	0.478 + j0.314	0.128 + j0.052	4390	375/400	435/490
500	0.022	0.030	0.032	0.037	0.478 + j0.314	0.128 + j0.052	4786	450/485	535/600
750	0.014	0.023	0.028	0.035	0.478 + j0.297	0.133 + j0.049	5372	545/585	670/745

* NEC ampacities are based on:

* For Duct: Table 310.60(C)(13) Detail 1.

* For Free Air: Table 310.60(C)(5).

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.





-
- * Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.
 - * Capacitive Reactance is between Phase-to-Shield.

