



AL Compact 35kV NLEPR Insulation 100% IL Black SIM-PVC Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Single Conductor Aluminum, 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level, Tape Shield, SIMpull Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
3. **Insulation:** 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 35KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend when UL listed. Rated at -25°C for cold bend and cold impact and marked with "LTDD" when CSA listed or dual UL/CSA listed. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)





- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE SIMpull® POWER CABLE {UL} XXXX KCMIL COMPACT AL--- {ALUMAFLEX}® AA8176 345 MILS NL-EPR 35KV 100% INS LEVEL 25%TS MV-105 FOR CT USE SUN RES (NESC) -- {CSA} 1000 KCMIL COMPACT AL--- {ALUMAFLEX}® AA8176 8.76mm (345 mils) NL-EPR 35KV 100% INS LEVEL 25%TS SR TC-ER 105°C FT4 -25°C LTDD -- PAT www.patentSW.com -- RoHS

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Copper Weight	Aluminum Weight	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size
	AWG/Kcmil	No. of Strands	inch	inch	inch	mil	inch	lb/1000ft	lb/1000ft	lb/1000ft	lb	inch	inch
649559	1/0	10	0.336	1.064	1.124	80	1.304	90	99	825	633	15.6	4.0
TBA	2/0	15	0.376	1.104	1.211	80	1.344	23	158	841	798	16.1	4.0
649569	3/0	15	0.422	1.151	1.211	80	1.391	96	158	958	1006	16.6	4.0
583741	4/0	19	0.474	1.203	1.263	80	1.443	100	199	1043	1269	17.3	4.0
580896	250	22	0.520	1.256	1.316	80	1.496	104	235	1127	1500	17.9	4.5
649572	350	35	0.615	1.352	1.412	80	1.592	111	329	1303	2100	19.1	4.5
580895	500	35	0.735	1.494	1.554	110	1.794	122	471	1667	3000	21.5	5.0
597511	750	58	0.908	1.666	1.726	110	1.966	134	706	2064	4500	23.5	5.5
597784	1000	58	1.060	1.818	1.878	110	2.128	146	942	2451	6000	25.5	6.0

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0	0.168	0.211	0.060	0.053	0.360 + j0.264	0.024 + j0.034	3513	155/165	200/225
2/0	0.133	0.167	0.056	0.051	0.570 + j0.463	0.204 + j0.051	3637	175/190	230/260
3/0	0.105	0.133	0.052	0.049	0.361 + j0.246	0.034 + j0.038	3779	200/215	270/300
4/0	0.084	0.105	0.048	0.047	0.361 + j0.250	0.031 + j0.038	3941	230/245	310/345
250	0.071	0.090	0.046	0.046	0.361 + j0.250	0.031 + j0.038	4108	250/270	345/380
350	0.050	0.065	0.040	0.044	0.427 + j0.421	0.056 + j0.034	4402	305/330	430/475
500	0.035	0.046	0.036	0.042	0.361 + j0.250	0.031 + j0.038	4774	370/400	530/590
750	0.024	0.033	0.031	0.039	0.361 + j0.250	0.031 + j0.038	5341	455/490	685/765
1000	0.018	0.026	0.027	0.037	0.361 + j0.264	0.024 + j0.034	5812	525/565	825/920

* NEC ampacities are based on:

* For Duct: Table 310.60(C)(12) Detail 1.

* For Free Air: Table 310.60(C)(4).

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.





-
- * Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.
 - * Capacitive Reactance is between Phase-to-Shield.

