Duraclad® Type MC THHN/THWN Circuit Size Copper Conductor 120/208V Colors Dashed-Blue Armor

Copper THHN/THWN Insulated Singles. Green Insulated Copper Grounding Conductor. UL Listed 600 Volts. Rated VW-1. Lightweight Steel Dashed-Blue Interlocked Armor.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid or 19 strands class C compressed copper per ASTM B3 and ASTM B8
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Ground:** Green insulated ground. Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
4. **Binder:** Mylar tape
5. **Armor:** Lightweight Steel Dashed-Blue Interlocked Armor

APPLICATIONS AND FEATURES:

Southwire Armorlite® Type MC Cable is suitable for use as follows:

- Branch, feeder and service power distribution in commercial, industrial, institutional, and multi- residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2)
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Binder tape with print legend wrapped around assembly.
- Type THHN/THWN rated 90ºC Dry.

Southwire Armorlite® Type MC Cable - meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables

Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

UPDATED: Sept. 17, 2025, 2:50 p.m.UTC REVISION: 1.000.005

- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

SOUTHWIRE E96627 {UL} TYPE MC XX AWG THHN OR THWN CDRS FOR USE IN CABLE TRAYS 600 VOLTS

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Diameter Over Armor	Copper Weight	Overall Weight
	AWG/ Kcmil			inch		mils	No. x AWG	inch	lbs/1000ft	lbs/1000ft
14 AWG | SOLID Strands										
643950	14	3	BK,RD,WE	0.064	SOLID	15	1x14	0.478	50	143
12 AWG | SOLID Strands										
571106	12	2	RD,WE	0.081	SOLID	15	1x12	0.484	60	154
571097	12	2	BK,WE	0.081	SOLID	15	1x12	0.484	60	154
571111	12	3	BK,RD,WE	0.081	SOLID	15	1x12	0.515	80	184
571148	12	4	BK,RD,BE,WE	0.081	SOLID	15	1x12	0.55	100	213
10 AWG | SOLID Strands										
571150	10	2	BK,WE	0.102	SOLID	20	1x10	0.551	93	205
588905	10	2	BK,BE	0.102	SOLID	20	1x10	0.55	93	205
571153	10	2	RD,WE	0.102	SOLID	20	1x10	0.55	93	205
571155	10	3	BK,RD,WE	0.102	SOLID	20	1x10	0.59	124	252
571159	10	3	BK,BE,WE	0.102	SOLID	20	1x10	0.59	124	252
571160	10	4	BK,RD,BE,WE	0.102	SOLID	20	1x10	0.634	155	297
12 AWG | 19 Strands										
574470	12	2	BK,WE	0.09	19	15	1x12	0.505	60	158
10 AWG | 19 Strands										
640694	10	4	BK,RD,BE,WE	0.117	19	20	1x10	0.675	162	322

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Note: Conductor number = number of phase conductors plus neutral. Does not include green ground.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/ Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
14 AWG | SOLID Strands							
14	3	3.3	2.631	3.265	0.058	20	25
12 AWG | SOLID Strands							
12	2	3.4	1.662	2.063	0.054	25	30
12	2	3.4	1.662	2.063	0.054	25	30
12	3	3.6	1.662	2.063	0.054	25	30
12	4	3.9	1.662	2.063	0.054	20	24
10 AWG | SOLID Strands							
10	2	3.9	1.04	1.291	0.05	35	40
10	2	3.9	1.04	1.291	0.05	35	40
10	2	3.9	1.04	1.291	0.05	35	40
10	3	4.1	1.04	1.291	0.05	35	40
10	3	4.1	1.04	1.291	0.05	35	40
10	4	4.4	1.04	1.291	0.05	28	32
12 AWG | 19 Strands							
12	2	3.5	1.662	2.063	0.054	25	30
10 AWG | 19 Strands							
10	4	4.7	1.04	1.291	0.05	28	32

***** Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

***** Ampacities have been adjusted for more than Three Current-Carrying Conductors.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved