

# **Duraclad® Type MC THHN/THWN Copper Conductor Feeder Cable**

## **277/480 Colors**

Copper THHN/THWN-2 Insulated Singles. Green or Bare Copper Grounding Conductor. UL Listed 600 Volts. Rated VW-1. Lightweight Galvanized Steel Interlocked Armor.




Image not to scale. See Table 1 for dimensions.

### **CONSTRUCTION:**

- Conductor:** Class B compressed copper per ASTM B3 and ASTM B8
- Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
- Ground:** Green insulated or bare stranded copper ground
- Filler:** Fillers as needed
- Binder:** Mylar tape
- Armor:** Galvanized Steel Interlocked Armor

### **APPLICATIONS AND FEATURES:**

#### **Southwire Armorlite® Type MC Feeder Cable is suitable for use as follows:**

- Feeder and service power distribution in commercial, industrial, institutional, and multi-residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2)
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Binder tape with print legend wrapped around assembly.
- Type THHN/THWN rated 90°C Dry.

#### **Southwire Duralclad® Type MC Cable - meets or exceeds the following requirements:**

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) ( [www.ul.com](http://www.ul.com) )
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

**Color Code - 3/C:** Brown, Orange, Yellow

**- 4/C:** Brown, Orange, Yellow, Gray

### **SPECIFICATIONS:**





- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- RoHS-2 (European Directive 2011/65/EU)
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

**SAMPLE PRINT LEGEND:**

E96627 {UL} TYPE MC AWG XX THHN OR THWN CDRS FOR USE IN CABLE TRAYS 600 VOLTS

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Diameter Over Armor	Copper Weight	Overall Weight
	AWG/ Kcmil			inch		mils	No. x AVG	inch	lbs/1000ft	lbs/1000ft
665920	3/0	3	BN,OE,YW	0.456	19	50	1x4 GG	1.506	1699	2369
677966	4/0	3	BN,OE,YW	0.512	19	60	1x4 GG	1.543	2109	2908
677486	250	4	TAN,PK,PE,GY/ WE,GN	0.558	37	70	1x4	1.962	3248	4390
646936	350	3	BN,OE,YW,GN	0.661	37	70	1x1/0	2.034	3603	4721
678473	400	3	BN,OE,YW	0.705	37	60	1x1/0 GG	2.168	4071	5054
644588	500	3	BN,OE,YW,GN	0.789	37	70	1x1/0	2.275	5007	6269
677968◊	600	3	BN,OE,YW	0.865	61	80	1x1/0 GG	2.395	5942	7285

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**Note:** Conductor number = number of phase conductors. Does not include ground

**Note:** GG = Green insulated ground

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 2 – Electrical and Engineering Data**

Cond. Size	Conductor Number	Min. Bend Radius	Max Pull Tension	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/ Kcmil		Inches	Lbs	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
3/0	3	10.5	4027	0.064	0.078	0.042	200	225
4/0	3	10.8	5078	0.051	0.062	0.041	230	260
250	4	13.7	6400	0.043	0.053	0.041	204	232
350	3	14.2	8400	0.031	0.039	0.04	310	350
400	3	15.2	9600	0.027	0.035	0.04	335	380
500	3	15.9	12000	0.022	0.029	0.039	380	430
600	3	16.8	14400	0.018	0.025	0.039	420	475

\* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

