



Duplex Copper XLPE Service Drop Neutral - Messenger

Copper Conductors With Crosslinked Polyethylene Insulation.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Conductors are stranded, compressed copper
2. **Insulation:** Cross Linked Polyethylene (XLPE)
3. **Messenger:** Hard Drawn Copper

APPLICATIONS AND FEATURES:

Primarily used for 120 volt overhead service applications such as street lighting, outdoor lighting, and temporary service for construction. To be used at voltages of 600 volts phase-to-phase or less and at conductor temperatures not to exceed 90°C for crosslinked polyethylene (XLP) insulated conductors.

SPECIFICATIONS:

- ASTM B1 Hard-Drawn Copper
- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ICEA S-76-474 Standard for Neutral-Supported Power Cable Assemblies with Weather-Resistant Extruded Insulation Rated 600V

Table 1 – Weights and Measurements

Stock Number	Code Word	Phase Cond. Size	Phase Strand	Dia. Over Phase Conductor	Phase Insul. Thickness	Dia. Over Phase Insulation	Neutral Cond. Size	Neutral Strand	Approx. OD	Approx. Weight
		AWG/Kcmil	No.	inch	mil	inch	AWG/Kcmil	No.	inch	lb/1000ft
TBA	Omega	8	Solid	0.128	30	0.188	8	1	0.378	180
TBA	Theta	8	7	0.141	30	0.201			0.404	131
TBA	Iota	8	7	0.141	30	0.201	8	1	0.404	182
TBA	Kappa	8	7	0.141	30	0.201	8	7	0.404	182
110650	Sigma	6	7	0.177	30	0.237	6	7	0.451	176
TBA	Lambda	6	7	0.177	30	0.237	8	1	0.476	251
TBA	Omicron	6	7	0.177	30	0.237	6	1	0.476	281

All dimensions are nominal and subject to normal manufacturing tolerances

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.





Table 2 – Electrical and Engineering Data

Code Word	Phase Cond. Size	Neutral Rated Breaking Strength	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	GMR	Allowable Ampacity In Air 75/90°C
	AWG/Kcmil	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	ft	Amp
Omega	8	826	0.653	0.786	0.052	0.004	70 / 80
Theta	8		0.653	0.786	0.052	0.004	70 / 80
Iota	8	826	0.653	0.786	0.052	0.004	70 / 80
Kappa	8	777	0.653	0.786	0.052	0.004	70 / 80
Sigma	6	1228	0.411	0.495	0.051	0.005	95 / 105
Lambda	6	826	0.411	0.495	0.051	0.005	95 / 105
Omicron	6	1280	0.411	0.495	0.051	0.005	95 / 105

