



## CU 1000V LSZH Insulation. RW90

Single Copper Conductors, LSZH Insulation Solonon®, Sunlight Resistant, 1000V, 90°C MAX, -40°C MIN, Gasoline & Oil Resistant



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
- Insulation:** Low Smoke Zero Halogen Solonon® (XLPO)

### APPLICATIONS AND FEATURES:

Suitable for installation in Cable Trays, Underground Duct Banks - As per CE Code limitations (see Rule 12-2202) for grounding and bonding applications. Standard colour is black. Some sizes may be available in white, red, blue, yellow, brown, orange or grey. Green Duraground™ also available.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- CSA C22.2 No.230 Tray Cables - Rated TC
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA SUN RES - for Sunlight Resistant rating
- CSA ST1 Smoke Test - marked FT4-ST1 (1/0 and Larger)
- Oil Res I & Sun Res - AWG 8 & Larger
- NFPA 130 Standard for Fixed Guideway Transit and Passenger Rail Systems (500kcmil & Larger)
- NFPA 502 Standard for Road Tunnels, Bridges, and Other Limited Access Highways

### SAMPLE PRINT LEGEND:

SOUTHWIRE SOLONONplus{TM} LSZH XLPO 156205 {CSA} XXX KCMIL (XXX{mm2}) CU RW90 1000V VW-1 HAL-FREE TC  
PRI PRII GRI GRII -40°C SR FT4 ST-1

**Table 1 – Weights and Measurements**

Cond. Size	Strand	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C†
AWG/ Kcmil	No.	mil	inch	lb/1000ft	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp
750	61	90	1.148	2471	5.7	6000	0.014	0.022	0.038	535





All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**Table 2 – Weights and Measurements (Metric)**

Cond. Size	Strand	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C
AWG/ Kcmil	No.	mm	mm	kg/km	mm	newton	Ω/km	Ω/km	Ω/km	Amp
750	61	2.29	29.16	3677	144.78	26700	0.05	0.07	0.1247	535

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

