



# CU Compressed 5/8kV NLEPR Insulation 133/100% IL AIA LSZH-TP Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Three Conductor Copper, 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, Aluminum Interlocked Armor (AIA), Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP) Jacket. Silicone Free



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
7. **Filler:** Wax paper filler
8. **Binder:** Polypropylene tape
9. **Armor:** Aluminum Interlocked Armor (AIA)
10. **Overall Jacket:** Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP)

## APPLICATIONS AND FEATURES:

Southwire's 5KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -25°C for cold bend. For uses in Class I and II, Division 2 hazardous locations per NEC Article 501 and 502. Rated for 1000 lbs./FT maximum sidewall pressure.

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4-ST1 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV





- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

**SAMPLE PRINT LEGEND:**

{SQFTG\_DUAL} SOUTHWIRE® POWER CABLE {UL} 3/C XX KCMIL CU 115 MILS NL-EPR 5KV 133%/8KV 100% INS LEVEL 25%TS GW 1 X XX AWG CU MV-105 OR MC FOR CT USE SUN. RES. FOR DIRECT BURIAL {NESC}

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Ground	Diameter Over armor	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius
	AWG/Kcmil	No. of Strands	inch	inch	inch	No. x AWG	inch	mil	inch	lb/1000ft	lb/1000ft	lb	inch
592657	4/0	19	0.512	0.766	0.826	1x3	2.160	60	2.286	2348	3736	5078	16.0

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◊ Cable marked with this symbol is a standard stock item

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
4/0	0.051	0.065	0.021	0.034	0.439 + j0.399	0.065 + j0.034	2633	265/280	285/320

- \* NEC ampacities are based on:
- \* For Duct: Table 310.60(C)(13) Detail 1.
- \* For Free Air: Table 310.60(C)(5).
- \* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
- \* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.
- \* Capacitive Reactance is between Phase-to-Shield.

