



Category 5E CMP




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Bare solid copper
2. **Insulation:** Fluorinated Polyethylene FPE
3. **Rip Cord:** Rip cord for ease of jacket removal
4. **Jacket:** Polyvinyl Chloride PVC.

APPLICATIONS AND FEATURES:

Southwire Cat 5E unshielded twisted pair cable is a high performance data communication cable. This ethernet cable is designed for indoor network installations TYPE CMP. It may be used in Ethernet Networking system, Video MPEG4 / M-JPEG / Digital / Analog / Baseband / Broadband and other Multimedia Voice applications.

- DC Resistance: <9.38 ohm/100m
- DC Resistance Unbalance: <5.00%
- Mutual Capacitance: <5.60 nF/100m
- Capacitance Unbalance (Pair to Ground): <330 pF/100m
- Insulation Resistance: >500 MOhm-100m
- Dielectric Strength: 2.5 DCkV/sec
- Impedance (mean): >100+/- 15% (1 < freq < 350MHz)
- Propagation Delay: <534 ns/100m
- Propagation Delay Skew: <45 ns/100m

SPECIFICATIONS:

- UL 444 Listed CMP
- IEEE 802.3 and IEC 61156-5 Ed. 2.0
- RoHS-3 Complies with European Directive 2015/863
- NFPA 262
- TIA/EIA 568.D.2 test to 350MHz , beyond 100MHz only for reference
- NEC Article 800

SAMPLE PRINT LEGEND:

SOUTHWIRE® SIGNAL®966956 CAT5E 24 AWG 4PR UTP E118871-LBI C(UL)US TYPE CMP 75C -- CMP FT6 TESTED TO 350 MHZ ETL VERIFIED TO TIA/EIA-568.D.2 CAT5E -- 0000FT -- MM/DD/YY HH:MM





Table 1 – Weights and Measurements

Stock Number	Cond. Size AWG/Kcmil	Number of Pairs pair	Jacket Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft
966956	24	4	14	0.185	20

All dimensions are nominal and subject to normal manufacturing tolerances
 ◊ Cable marked with this symbol is a standard stock item

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size AWG/Kcmil	Number of Pairs pair	Jacket Thickness mm	Approx. OD mm	Approx. Weight lb/km
966956	24	4	0.36	4.70	30

Electrical Performance

Freq. (MHz)	Attenuation (dB/100m)Max	NEXT (dB/100m) Min	PSNEXT (dB/100m)Min	ELFEXT (dB/100m)Min	PSELFEXT (dB/100m)Min	RL (dB/100m) Min	P.Delay (ns/100m)Max
1	2	65.3	62.3	63.8	60.8	20	570
4	4.1	56.3	53.3	51.8	48.8	23	552
8	5.8	51.8	48.8	45.7	42.7	24.5	547
10	6.5	50.3	47.3	43.8	40.8	25	545
16	8.2	47.2	44.2	39.7	36.7	25	543
20	9.3	45.8	42.8	37.8	34.8	25	542
25	10.4	44.3	41.3	35.8	32.8	24.3	541
31.25	11.7	42.9	39.9	33.9	30.9	23.6	540
62.5	17	38.4	35.4	27.9	24.9	21.5	539
100	22	35.3	32.3	23.8	20.8	20.1	538
200	32.4	30.8	27.8	17.8	14.8	18	537
350	44.9	27.1	24.1	12.9	9.9	16.3	536

