



Armorlite® Type MC THHN/THWN Circuit Size Copper Conductor Neutral Per Phase

Copper THHN/THWN Insulated Singles. Dedicated Neutral Conductor for Each Phase Conductor. Green Insulated Copper Grounding Conductor. UL Listed 600 Volts. Rated VW-1. Lightweight Aluminum Interlocked Armor.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid or 19 strands class C compressed copper per ASTM B3 and ASTM B8
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Ground:** Green insulated ground. Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
4. **Binder:** Mylar tape
5. **Aarmor:** Aluminum Interlocked Armor

Contact [Southwire SPEED™ Services](#) to request a quote.

APPLICATIONS AND FEATURES:

Southwire Armorlite® Type MC Cable Neutral-per-phase products comply with NEC 200.4 requirements (added in the 2011 NEC) for the installation and marking of neutral conductors. Neutrals are not to be used for more than one circuit (branch, multiwire branch, or ungrounded feeder). See NEC 200.4 for complete requirements.

Southwire Armorlite® Type MC Cable - Neutral per phase is suitable for use as follow:

- Applications affected by harmonics generated from non-linear switching loads, such as computers, variable frequency drives, electrical test equipment, and office equipment.
- Multiple circuits for branch, feeder and service power distribution in commercial, industrial, institutional, and multi-residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2)
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Binder tape with print legend wrapped around assembly.
- Type THHN/THWN rated 90°C Dry.

Southwire Armorlite® Type MC Cable -Neutral per phase meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)





- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

E96627 {UL} TYPE MC XX AWG THHN OR THWN CDRS FOR USE IN CABLE TRAYS 600 VOLTS

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Num x Neutral Size	Diameter Over Armor	Copper Weight	Overall Weight
	AWG/ Kcmil		inch		mils	No. x AWG	No. x AWG	inch	lbs/1000ft	lbs/1000ft
10 AWG Solid										
567269	10	4	0.101	Solid	25	1x10	4x10	0.823	278	425

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Note: Conductor number = number of phase conductors. Does not include neutrals and green ground.

Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/ Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
10 AWG Solid							
10	4	5.8	1.040	1.253	0.050	24	28

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.





Color Table

Stock Num.	Cond. Size	Cond. Num.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17
674349	14	2	Black	Red	Green	White	Red												
554994	12	2	Red	Green	White														
551322	12	2	Black	Red	Green	White	Red	Green											
552795	12	4	Black	Red	Green	White	Red												
554991	12	2	Black	Red	Green	White	Red												
566801	12	2	Black	Red	Green	White	Red												
610666	12	2	Black	Red	Green	White	Red	Green											
551324	12	3	Black	Red	Blue	Green	White	Red	Blue	Green									
551353	12	4	Black	Red	White	Black	Green	White	Red										
554990	12	3	Black	Red	Blue	Green	White	Red	Blue										
562687	12	3	Black	Red	Blue	Green	White	Red	Blue										
610669	12	3	Black	Red	Blue	Green	White	Red	Blue	Green									
566811	12	4	Black	Red	Blue	White	Black	Green	White	Red	Blue								
643570	12	4	Black	Red	Blue	Purple	White	Red	Blue	Purple									
589122	12	6	Black	Red	Blue	White	Black	Red	Blue	Green	White	Red	Blue						
580850	12	6	Black	Red	Blue	White	Black	Red	Blue	Green	2X	2X	White						
643654	12	6	Black	Red	Blue	Yellow	Pink	Purple	Green	White	Red	Blue	Yellow	Pink	Purple				
674313	12	7	Black	Red	Blue	White	Black	Red	Blue	Green	2X	2X	2X						
679370	12	10	3X Black	Red	3X White	Black	Red	Red	Red	Blue	Blue	Green	White	Red	Blue				
641211	12	9	3X Black	3X Red	3X Blue	9X White	Green												
552996	10	2	Black	Red	White	Green	Blue	Green											
563822	10	2	Black	Red	Green	White	Red												
567063	10	2	Black	Red	Green	White	Red												
586636	10	2	Black	Red	Green	White	Red	Green											
641220	10	2	Black	Red	Green	White	Red	Green											
551336	10	3	Black	Red	Blue	Green	White	Red	Blue	Green									
553238	10	3	Black	Red	Blue	White	Green	White	Red										
556259	10	3	Black	Red	Blue	Green	White	Red	Blue										
562456	10	3	Black	Red	Blue	Green	White	Red	Blue										
592678	10	3	Black	Red	Blue	Green	White	Red	Blue										
610673	10	3	Black	Red	Blue	Green	White	Red	Blue	Green									
674737	10	4	Black	Red	White	Black	Red	Green	White										





Stock Num.	Cond. Size	Cond. Num.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17
551356	10	8																	
554852	10	4																	
566698	10	4																	
640523	10	5																	
585848	10	5																	
590115	10	5	2X 	2X 			2X 	2X 											
598031	10	6																	
677655	10	5																	
647488	10	6	6X 	6X 															
679158	10	7																	
647335	10	8	8X 	8X 															
679161	10	16																	

