# Flexible Hook-Up Wire/Appliance Wire Styles 1007/1569 or 1581/1589

80°C or 105°C Dry. 300 Volts. Flexible Stranded Copper Conductor. PVC Insulation.





Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class K, stranded bare copper or tinned copper per ASTM B3 or B8 and B174
2. **Insulation:** Polyvinyl Chloride (PVC). All colors available; Stripes available upon request

## APPLICATIONS AND FEATURES:

For us in internal wiring of appliances or electronic equipment where not subject to movement or mechanical damage.

- AWM Style 1007: 80°C Dry, 300V. 24 - 16 AWG
- AWM Style 1569: 105°C Dry, 300V
- TR-64: 90°C Dry. 24 - 14 AWG
- AWM I A/B: 105°C Dry, 300V
- AWM Style 1581: 80°C Dry, 300V. 14 - 10 AWG
- Rated for VW-1 and FT1

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 758 Standard for Appliance Wiring Material
- CSA C22.2 No. 127 Equipment and Lead Wires
- CSA C22.2 No. 210 Appliance Wiring Material Products

## SAMPLE PRINT LEGEND:

24 - 16 AWG:
XX AWG (XX{mm2}) E57498 {RU} AWM 1569 105C OR 1007 80C 300V VW-1 -- 156205 {CSA} TR-64 90°C FT1 OR AWM I A/B 105C 300V FT1
14 AWG:
14 AWG (2.08mm2) E57498 {RU} AWM 1569 105C OR 1581 80C 300V VW-1 -- 156205 {CSA} TR-64 90C FT1 OR AMW I A/B 105C 300V FT1
12 - 10 AWG:
XX AWG (XXmm2) E57498 {RU} 1569 105C OR 1581 80C 300V VW-1 -- 156205 {CSA} AWM I A/B 105C 300V FT1



Copyright © 2026 Southwire Company, LLC. All Rights Reserved

## Table 1 – Physical and Electrical Data

| Stock Number | Cond. Size | Cond. Number | Cond. Strands | Cond. Metal | Diameter Over Cond. | Insul. Thickness | Approx. OD | Approx. Weight | DC Resistance @ 25°C | AC Resistance @ 75°C |
|---|---|---|---|---|---|---|---|---|---|---|
| | AWG | No. | strands | | inch | mil | inch | lb /1000ft | Ω /1000ft | Ω /1000ft |
| AWM | | | | | | | | | | |
| F14028 | 14 | 1 | 41 | TCu | 0.073 | 16 | 0.110 | 15 | 2.814 | 3.391 |

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Ampacity


Copyright © 2026 Southwire Company, LLC. All Rights Reserved