ACSR/AW

Aluminum Conductor, Aluminum-Clad Steel Reinforced




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Core:** Stranded standard strength aluminum-clad steel core
2. **Stranding:** Hard-drawn aluminum (1350-H19) round wire shaped strands with 61.2% conductivity

APPLICATIONS AND FEATURES:

ACSR/AW (Aluminum Conductor, Aluminum-Clad Steel Reinforced) is a concentrically stranded conductor consisting of one or more layers of hard-drawn aluminum (1350-H19) wires surrounding an aluminum-clad steel core. The aluminum strands provide efficient electrical conductivity, while the aluminum-clad steel core supplies strength, improved sag performance, and enhanced corrosion resistance. ACSR/AW is widely used for overhead transmission and distribution applications where a combination of ampacity, strength, corrosion protection, and long-term reliability is required.

Continuous operating temperature - 75°C
Emergency operating temperature - 100°C

SPECIFICATIONS:

- ASTM B230 Standard Specification for Aluminum 1350-H19 Wire for Electrical Purposes
- ASTM B502 Standard Specification for Aluminum-Clad Steel Core Wire for Use in Overhead Electrical Aluminum Conductors
- ASTM B549 Standard Specification for Concentric-Lay-Stranded Aluminum Conductors, Aluminum-Clad Steel Reinforced (ACSR/AW)

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Weights, Measurements, Electrical and Engineering Data

Stock Number	Code Word	Conductor Size	Stranding	Cross-Sectional Area		Layers of Al	Diameter				Weight		Rated Breaking Strength		DC Resistance @ 20°C
				Al	Total		Individual Strands		AW Core	Complete Conductor	Al	Total	AW2	AW3	
		AWG/kcmil	Al/AW	in²	in²		in	in	in	in	lb/ 1000ft	lb/ 1000ft	lb	lb	Ω/mile
TBA	SWAN/AW	4	6/1	0.0328	0.0383	1	0.0834	0.0834	0.0834	0.250	38.95	54.66	1,780	1,860	2.0583
TBA	SWANATE/AW	4	7/1	0.0328	0.0411	1	0.0772	0.1029	0.1029	0.257	38.95	62.66	2,280	2,360	2.0037
TBA	SPARROW/AW	2	6/1	0.0522	0.0609	1	0.1052	0.1052	0.1052	0.316	61.99	86.85	2,760	2,850	1.2937
TBA	SPARATE/AW	2	7/1	0.0522	0.0655	1	0.0974	0.1299	0.1299	0.325	61.99	99.99	3,510	3,640	1.2583
TBA	ROBIN/AW	1	6/1	0.0657	0.0767	1	0.1181	0.1181	0.1181	0.354	78.02	109.5	3,450	3,550	1.0277
TBA	RAVEN/AW	1/0	6/1	0.0830	0.0968	1	0.1327	0.1327	0.1327	0.398	98.57	138.0	4,250	4,380	0.8138
TBA	QUAIL/AW	2/0	6/1	0.1045	0.1219	1	0.1489	0.1489	0.1489	0.447	124.1	173.8	5,130	5,300	0.6463
TBA	PIGEON/AW	3/0	6/1	0.1317	0.1537	1	0.1672	0.1672	0.1672	0.502	156.4	219.3	6,300	6,620	0.5127
TBA	PENGUIN/AW	4/0	6/1	0.1662	0.1939	1	0.1878	0.1878	0.1878	0.563	197.4	276.5	7,690	8,350	0.4063
TBA	MAGPIE/AW	20.87	3/4	0.0164	0.0383	0.5	0.0834	0.0834	---	0.250	19.48	82.74	4,100	4,420	3.0091
TBA	SHRIKE/AW	33.185	3/4	0.0261	0.0609	0.5	0.1052	0.1052	---	0.316	31.00	131.5	6,490	6,830	1.8917
TBA	SNIPE/AW	52.77	3/4	0.0414	0.0966	0.5	0.1326	0.1326	---	0.398	49.16	208.7	10,000	10,500	1.1926
TBA	ALBATROSS/AW	54.95	7/1	0.0432	0.0542	1	0.0886	0.1181	0.1181	0.295	51.30	82.73	2,980	3,080	1.5206
TBA	SHOEBILL/AW	57.50	3/4	0.0451	0.1053	0.5	0.1384	0.1384	---	0.415	53.56	227.5	10,600	11,500	1.0944
TBA	LOON/AW	66.54	3/4	0.0522	0.1219	0.5	0.1489	0.1489	---	0.447	61.99	263.3	11,900	12,600	0.9454
TBA	GROUSE/AW	80.00	8/1	0.0628	0.0846	1	0.1000	0.1667	0.1667	0.367	74.95	137.2	4,880	5,190	1.0213
TBA	PETREL/AW	101.8	12/7	0.0799	0.1265	1	0.0921	0.0921	0.2763	0.461	95.82	229.5	9,910	10,400	0.7526
TBA	MINORCA/AW	110.8	12/7	0.0870	0.1378	1	0.0961	0.0961	0.2883	0.481	104.3	250.0	10,800	11,300	0.6911
TBA	LEGHORN/AW	134.6	12/7	0.1057	0.1674	1	0.1059	0.1059	0.3177	0.530	126.8	303.8	13,000	13,600	0.5689
TBA	GUINEA/AW	159.0	12/7	0.1249	0.1977	1	0.1151	0.1151	0.3453	0.576	149.8	358.6	15,300	16,000	0.4815
TBA	DOTTEREL/AW	176.9	12/7	0.1389	0.2199	1	0.1214	0.1214	0.3642	0.607	166.6	399.0	16,900	17,300	0.4330
TBA	DORKING/AW	190.8	12/7	0.1499	0.2373	1	0.1261	0.1261	0.3783	0.631	179.8	430.5	18,300	18,700	0.4012
TBA	AUK/AW	203.0	8/7	0.1594	0.2025	1	0.1593	0.0885	0.2655	0.584	190.2	313.8	10,900	11,500	0.4121
TBA	BRAHMA/AW	203.2	16/19	0.1596	0.3020	1	0.1127	0.0977	0.4885	0.714	191.4	600.7	27,100	28,400	0.3466
TBA	COCHIN/AW	211.3	12/7	0.1660	0.2628	1	0.1327	0.1327	0.3981	0.664	199.1	476.8	19,800	20,700	0.3623
TBA	JAEGER/AW	228.2	18/1	0.1792	0.1892	2	0.1126	0.1126	0.1126	0.563	213.9	242.5	5,920	6,020	0.3926
TBA	WAXWING/AW	266.8	18/1	0.2094	0.2210	2	0.1217	0.1217	0.1217	0.609	249.9	283.0	6,820	6,880	0.3360
TBA	PARTRIDGE/AW	266.8	26/7	0.2095	0.2436	2	0.1013	0.0788	0.2364	0.642	251.2	349.0	10,800	11,300	0.3258
TBA	JUNCO/AW	266.8	30/7	0.2095	0.2584	2	0.0943	0.0943	0.2829	0.660	251.9	392.2	13,500	13,900	0.3193
TBA	OSTRICH/AW	300.0	26/7	0.2355	0.2738	2	0.1074	0.0835	0.2505	0.680	282.4	392.3	12,100	12,700	0.2899
TBA	MERLIN/AW	336.4	18/1	0.2642	0.2789	2	0.1367	0.1367	0.1367	0.684	315.3	357.3	8,540	8,680	0.2663
TBA	WIDGEON/AW	336.4	24/7	0.2642	0.2984	2	0.1184	0.0789	0.2367	0.710	316.8	414.9	12,000	12,500	0.2612
TBA	LINNET/AW	336.4	26/7	0.2640	0.3070	2	0.1137	0.0884	0.2652	0.720	316.6	440.0	13,500	14,100	0.2586
TBA	ORIOLE/AW	336.4	30/7	0.2642	0.3259	2	0.1059	0.1059	0.3177	0.741	317.6	494.6	16,700	17,300	0.2532
TBA	CHICKADEE/AW	397.5	18/1	0.3122	0.3295	2	0.1486	0.1486	0.1486	0.743	372.6	422.0	9,780	9,940	0.2254
TBA	BRANT/AW	397.5	24/7	0.3122	0.3527	2	0.1287	0.0858	0.2574	0.772	374.4	490.6	14,100	14,600	0.2210
TBA	IBIS/AW	397.5	26/7	0.3120	0.3628	2	0.1236	0.0961	0.2883	0.783	374.2	519.9	15,800	16,300	0.2188
TBA	LARK/AW	397.5	30/7	0.3121	0.3849	2	0.1151	0.1151	0.3453	0.806	375.2	584.0	19,600	20,300	0.2144

We've got it MADE IN AMERICA

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Stock # 234914 | SPEC 80102

Stock Number	Code Word	Conductor Size	Stranding	Cross-Sectional Area		Layers of Al	Diameter				Weight		Rated Breaking Strength		DC Resistance @ 20°C
				Al	Total		Individual Strands		AW Core	Complete Conductor	Al	Total	AW2	AW3	
		AWG/kcmil	Al/AW	in²	in²		in	in	in	in	lb/1000ft	lb/1000ft	lb	lb	Ω/mile
TBA	PELICAN/AW	477.0	18/1	0.3747	0.3955	2	0.1628	0.1628	0.1628	0.814	447.2	506.6	11,500	11,800	0.1878
TBA	TOUCAN/AW	477.0	22/7	0.3744	0.4112	2	0.1472	0.0818	0.2454	0.834	449.0	554.6	14,700	15,200	0.1862
TBA	FLICKER/AW	477.0	24/7	0.3747	0.4233	2	0.1410	0.0940	0.2820	0.846	449.4	588.8	16,700	17,200	0.1841
TBA	HAWK/AW	477.0	26/7	0.3744	0.4354	2	0.1354	0.1053	0.3159	0.858	449.0	624.0	18,900	19,500	0.1823
TBA	HEN/AW	477.0	30/7	0.3747	0.4621	2	0.1261	0.1261	0.3783	0.883	450.5	701.2	23,400	23,800	0.1785
TBA	HERON/AW	500.0	30/7	0.3927	0.4843	2	0.1291	0.1291	0.3873	0.904	472.1	734.9	24,100	25,000	0.1704
TBA	OSPREY/AW	556.5	18/1	0.4369	0.4612	2	0.1758	0.1758	0.1758	0.879	521.4	590.8	13,200	13,700	0.1610
TBA	SAPSUCKER/AW	556.5	22/7	0.4368	0.4797	2	0.1590	0.0883	0.2649	0.901	523.8	646.9	17,000	17,600	0.1596
TBA	PARAKEET/AW	556.5	24/7	0.4372	0.4938	2	0.1523	0.1015	0.3045	0.914	524.3	686.7	19,300	19,800	0.1578
TBA	DOVE/AW	556.5	26/7	0.4371	0.5083	2	0.1463	0.1138	0.3414	0.927	524.2	728.4	21,900	22,600	0.1562
TBA	EAGLE/AW	556.5	30/7	0.4371	0.5391	2	0.1362	0.1362	0.4086	0.953	525.5	818.1	26,800	27,800	0.1531
TBA	PEACOCK/AW	605.0	24/7	0.4753	0.5370	2	0.1588	0.1059	0.3177	0.953	570.0	747.0	21,000	21,600	0.1452
TBA	SQUAB/AW	605.0	26/7	0.4749	0.5522	2	0.1525	0.1186	0.3558	0.966	569.5	791.2	23,600	24,300	0.1437
TBA	WOOD DUCK/AW	605.0	30/7	0.4751	0.5860	2	0.1420	0.1420	0.4260	0.994	571.2	889.3	28,400	28,900	0.1408
TBA	TEAL/AW	605.0	30/19	0.4751	0.5834	2	0.1420	0.0852	0.4260	0.994	571.2	882.5	28,500	30,000	0.1411
TBA	DUCK/AW	605.0	54/7	0.4747	0.5362	3	0.1058	0.1058	0.3174	0.952	569.3	745.7	21,600	22,200	0.1454
TBA	KINGBIRD/AW	636.0	18/1	0.4997	0.5275	2	0.1880	0.1880	0.1880	0.940	596.3	675.7	15,000	15,700	0.1408
TBA	SWIFT/AW	636.0	36/1	0.4994	0.5133	3	0.1329	0.1329	0.1329	0.930	596.0	635.7	13,600	13,800	0.1422
TBA	TURACOS/AW	636.0	20/7	0.4994	0.5339	2	0.1783	0.0792	0.2376	0.951	598.9	697.9	16,900	17,400	0.1409
TBA	GOLDFINCH/AW	636.0	22/7	0.4994	0.5484	2	0.1700	0.0944	0.2832	0.963	598.9	739.5	19,400	19,800	0.1396
TBA	ROOK/AW	636.0	24/7	0.4996	0.5643	2	0.1628	0.1085	0.3255	0.977	599.1	784.7	22,000	22,600	0.1381
TBA	GROSBEAK/AW	636.0	26/7	0.4995	0.5808	2	0.1564	0.1216	0.3648	0.990	599.0	832.2	24,800	25,200	0.1367
TBA	SCOTER/AW	636.0	30/7	0.4995	0.6160	2	0.1456	0.1456	0.4368	1.019	600.5	934.7	29,300	30,400	0.1339
TBA	EGRET/AW	636.0	30/19	0.4995	0.6135	2	0.1456	0.0874	0.4370	1.019	600.5	928.2	29,900	31,500	0.1342
TBA	GOOSE/AW	636.0	54/7	0.4993	0.5640	3	0.1085	0.1085	0.3255	0.977	598.8	784.4	22,700	23,300	0.1382
TBA	FLAMINGO/AW	666.6	24/7	0.5238	0.5917	2	0.1667	0.1111	0.3333	1.000	628.2	823.0	23,100	23,700	0.1317
TBA	GANNET/AW	666.6	26/7	0.5234	0.6086	2	0.1601	0.1245	0.3735	1.014	627.7	872.1	26,000	26,400	0.1304
TBA	GULL/AW	666.6	54/7	0.5235	0.5914	3	0.1111	0.1111	0.3333	1.000	627.8	822.6	23,500	24,200	0.1318
TBA	STILT/AW	715.5	24/7	0.5622	0.6350	2	0.1727	0.1151	0.3453	1.036	674.2	883.0	24,800	25,500	0.1227
TBA	STARLING/AW	715.5	26/7	0.5620	0.6535	2	0.1659	0.1290	0.3870	1.051	674.0	936.5	27,500	28,400	0.1215
TBA	REDWING/AW	715.5	30/19	0.5617	0.6897	2	0.1544	0.0926	0.4630	1.081	675.3	1043	33,400	34,600	0.1193
TBA	CROW/AW	715.5	54/7	0.5619	0.6347	3	0.1151	0.1151	0.3453	1.036	673.9	882.7	25,300	26,000	0.1228
TBA	COOT/AW	795.0	36/1	0.6244	0.6417	3	0.1486	0.1486	0.1486	1.040	745.2	794.6	16,600	16,800	0.1137
TBA	TURBIT/AW	795.0	20/7	0.6246	0.6678	2	0.1994	0.0886	0.2658	1.063	749.1	873.0	21,200	21,800	0.1127
TBA	PUFFIN/AW	795.0	22/7	0.6244	0.6857	2	0.1901	0.1056	0.3168	1.077	748.8	924.6	24,200	24,800	0.1116
TBA	CUCKOO/AW	795.0	24/7	0.6244	0.7053	2	0.1820	0.1213	0.3639	1.092	748.8	980.9	27,500	27,900	0.1105
TBA	DRAKE/AW	795.0	26/7	0.6247	0.7264	2	0.1749	0.1360	0.4080	1.108	749.2	1041	30,500	31,500	0.1093
TBA	SKIMMER/AW	795.0	30/7	0.6245	0.7702	2	0.1628	0.1628	0.4884	1.140	750.8	1169	35,600	37,700	0.1071
TBA	MALLARD/AW	795.0	30/19	0.6245	0.7669	2	0.1628	0.0977	0.4885	1.140	750.8	1160	37,100	38,400	0.1073
TBA	TERN/AW	795.0	45/7	0.6242	0.6674	3	0.1329	0.0886	0.2658	1.063	748.6	872.5	21,500	22,100	0.1128
TBA	CONDOR/AW	795.0	54/7	0.6240	0.7049	3	0.1213	0.1213	0.3639	1.092	748.3	980.4	27,800	28,200	0.1106
TBA	RUDDY/AW	900.0	45/7	0.7066	0.7555	3	0.1414	0.0943	0.2829	1.131	847.4	987.7	24,000	24,400	0.0996

We've got it
MADE IN AMERICA

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Stock # 234914 | SPEC 80102

Stock Number	Code Word	Conductor Size	Stranding	Cross-Sectional Area		Layers of Al	Diameter				Weight		Rated Breaking Strength		DC Resistance @ 20°C
				Al	Total		Individual Strands		AW Core	Complete Conductor	Al	Total	AW2	AW3	
		AWG/kcmil	Al/AW	in²	in²		in	in	in	in	lb/1000ft	lb/1000ft	lb	lb	Ω/mile
TBA	CANARY/AW	900.0	54/7	0.7069	0.7985	3	0.1291	0.1291	0.3873	1.162	847.7	1111	31,000	31,900	0.0976
TBA	CORNCRAKE/AW	954.0	20/7	0.7492	0.8010	2	0.2184	0.0971	0.2913	1.165	898.5	1047	25,100	25,600	0.0939
TBA	REDBIRD/AW	954.0	24/7	0.7495	0.8466	2	0.1994	0.1329	0.3987	1.196	898.8	1177	32,600	33,500	0.0921
TBA	MERGANSER/AW	954.0	30/7	0.7491	0.9239	2	0.1783	0.1783	0.5349	1.248	900.5	1402	41,900	45,200	0.0893
TBA	CANVASBACK/AW	954.0	30/19	0.7491	0.9199	2	0.1783	0.1070	0.5350	1.248	900.5	1391	44,500	46,100	0.0895
TBA	PHOENIX/AW	954.0	42/7	0.7491	0.7876	3	0.1507	0.0837	0.2511	1.155	898.4	1009	22,800	23,400	0.0945
TBA	RAIL/AW	954.0	45/7	0.7492	0.8010	3	0.1456	0.0971	0.2913	1.165	898.5	1047	25,400	25,900	0.0939
TBA	TOWHEE/AW	954.0	48/7	0.7495	0.8157	3	0.1410	0.1097	0.3291	1.175	898.8	1089	27,800	28,500	0.0933
TBA	CARDINAL/AW	954.0	54/7	0.7491	0.8462	3	0.1329	0.1329	0.3987	1.196	898.4	1177	32,900	33,800	0.0921
TBA	SNOWBIRD/AW	1033.5	42/7	0.8121	0.8539	3	0.1569	0.0872	0.2616	1.203	973.9	1094	24,800	25,400	0.0872
TBA	ORTOLAN/AW	1033.5	45/7	0.8112	0.8673	3	0.1515	0.1010	0.3030	1.212	972.8	1134	27,100	27,700	0.0868
TBA	WHOOPER/AW	1033.5	48/7	0.8113	0.8829	3	0.1467	0.1141	0.3423	1.223	973.0	1178	30,100	30,800	0.0862
TBA	CURLEW/AW	1033.5	54/7	0.8112	0.9164	3	0.1383	0.1383	0.4149	1.245	972.8	1275	35,100	36,600	0.0851
TBA	AVOCET/AW	1113.0	42/7	0.8743	0.9192	3	0.1628	0.0904	0.2712	1.248	1049	1178	26,600	27,100	0.0810
TBA	BLUEJAY/AW	1113.0	45/7	0.8745	0.9350	3	0.1573	0.1049	0.3147	1.259	1049	1223	29,300	29,800	0.0805
TBA	BULLFINCH/AW	1113.0	48/7	0.8744	0.9516	3	0.1523	0.1185	0.3555	1.269	1049	1271	32,100	32,800	0.0800
TBA	FINCH/AW	1113.0	54/19	0.8746	0.9855	3	0.1436	0.0862	0.4310	1.293	1054	1373	37,500	39,100	0.0793
TBA	OXBIRD/AW	1192.5	42/7	0.9366	0.9848	3	0.1685	0.0936	0.2808	1.292	1123	1261	28,500	29,000	0.0756
TBA	BUNTING/AW	1192.5	45/7	0.9367	1.0014	3	0.1628	0.1085	0.3255	1.302	1123	1309	31,300	32,000	0.0751
TBA	CORMORANT/AW	1192.5	48/7	0.9364	1.0190	3	0.1576	0.1226	0.3678	1.313	1123	1360	34,300	34,700	0.0747
TBA	GRACKLE/AW	1192.5	54/19	0.9365	1.0552	3	0.1486	0.0892	0.4460	1.338	1129	1470	40,200	41,900	0.0741
TBA	SCISSORTAIL/AW	1272.0	42/7	0.9987	1.0501	3	0.1740	0.0967	0.2901	1.334	1198	1345	30,400	30,900	0.0709
TBA	BITTERN/AW	1272.0	45/7	0.9987	1.0678	3	0.1681	0.1121	0.3363	1.345	1198	1396	33,400	34,100	0.0705
TBA	DIVER/AW	1272.0	48/7	0.9992	1.0873	3	0.1628	0.1266	0.3798	1.357	1198	1451	36,600	37,000	0.0700
TBA	PHEASANT/AW	1272.0	54/19	0.9993	1.1259	3	0.1535	0.0921	0.4605	1.382	1204	1568	42,400	43,600	0.0694
TBA	RINGDOVE/AW	1351.5	42/7	1.0617	1.1163	3	0.1794	0.0997	0.2991	1.376	1273	1430	32,400	32,900	0.0667
TBA	DIPPER/AW	1351.5	45/7	1.0614	1.1347	3	0.1733	0.1155	0.3465	1.386	1273	1483	35,500	36,200	0.0663
TBA	MARTIN/AW	1351.5	54/19	1.0614	1.1958	3	0.1582	0.0949	0.4745	1.424	1279	1665	45,100	46,300	0.0654
TBA	POPINJAY/AW	1431.0	42/7	1.1241	1.1820	3	0.1846	0.1026	0.3078	1.415	1348	1514	34,300	34,800	0.0630
TBA	BOBOLINK/AW	1431.0	45/7	1.1236	1.2013	3	0.1783	0.1189	0.3567	1.427	1347	1570	37,600	38,300	0.0626
TBA	WAGTAIL/AW	1431.0	48/7	1.1244	1.2236	3	0.1727	0.1343	0.4029	1.439	1348	1633	40,700	41,700	0.0622
TBA	PLOVER/AW	1431.0	54/19	1.1241	1.2665	3	0.1628	0.0977	0.4885	1.465	1355	1764	47,700	49,100	0.0617
TBA	NUTHATCH/AW	1510.5	45/7	1.1862	1.2682	3	0.1832	0.1221	0.3663	1.466	1423	1658	39,700	40,100	0.0593
TBA	PARROT/AW	1510.5	54/19	1.1856	1.3357	3	0.1672	0.1003	0.5015	1.505	1429	1860	50,300	51,700	0.0585
TBA	RATITE/AW	1590.0	42/7	1.2492	1.3134	3	0.1946	0.1081	0.3243	1.492	1498	1682	38,100	38,700	0.0567
TBA	LAPWING/AW	1590.0	45/7	1.2492	1.3355	3	0.1880	0.1253	0.3759	1.504	1498	1746	41,800	42,200	0.0563
TBA	HORNBILL/AW	1590.0	48/7	1.2487	1.3589	3	0.1820	0.1416	0.4248	1.517	1498	1814	44,700	45,300	0.0560
TBA	FALCON/AW	1590.0	54/19	1.2489	1.4072	3	0.1716	0.1030	0.5150	1.545	1505	1960	53,000	54,500	0.0556
TBA	CHUKAR/AW	1780.0	84/19	1.3986	1.5126	4	0.1456	0.0874	0.4370	1.602	1685	2013	49,400	51,000	0.0504

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Stock # 234914 | SPEC 80102

Stock Number	Code Word	Conductor Size	Stranding	Cross-Sectional Area		Layers of Al	Diameter				Weight		Rated Breaking Strength		DC Resistance @ 20°C
				Al	Total		Individual Strands		AW Core	Complete Conductor	Al	Total	AW2	AW3	
		AWG/kcmil	Al/AW	in²	in²		in	in	in	in	lb/1000ft	lb/1000ft	lb	lb	Ω/mile
TBA	WOODPECKER/AW	1843.0	72/7	1.4476	1.5102	4	0.1600	0.1067	0.3201	1.600	1745	1925	41,800	42,400	0.0493
TBA	SEAHAWK/AW	1869.0	68/7	1.4681	1.5147	4	0.1658	0.0921	0.2763	1.603	1769	1903	39,500	40,000	0.0488
TBA	MOCKINGBIRD/AW	2034.5	72/7	1.5979	1.6670	4	0.1681	0.1121	0.3363	1.681	1926	2124	46,100	46,800	0.0446
TBA	BLUEBIRD/AW	2156.0	84/19	1.6931	1.8309	4	0.1602	0.0961	0.4805	1.762	2040	2436	59,000	60,300	0.0416
TBA	KIWI/AW	2167.0	72/7	1.7022	1.7758	4	0.1735	0.1157	0.3471	1.735	2051	2262	49,100	49,800	0.0419
TBA	THRASHER/AW	2312.0	76/19	1.8155	1.9144	4	0.1744	0.0814	0.4070	1.802	2188	2472	55,300	56,700	0.0391
TBA	JOREE/AW	2515.0	76/19	1.9750	2.0826	4	0.1819	0.0849	0.4245	1.880	2380	2689	60,200	61,700	0.0360

Copyright © 2026 Southwire Company, LLC. All Rights Reserved