



CU 600/1000V XLPE Insulation ARMOR-X[®] Thermoplastic LSZH-TP Jacket XHHW-2. VFD Cable - CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free

Type MC-HL Power Cable 600 Volt Three Conductor Copper, Cross Linked Polyethylene (XLPE) insulation XHHW-2 Continuous Corrugated Welded Armor - ARMOR-X[®], Thermoplastic Solonon[®] Low Smoke Zero Halogen (LSZH-TP) Jacket with Bare CU Ground




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and B8
2. **Insulation:** Cross Linked Polyethylene (XLPE) Type XHHW-2
3. **Grounding Conductor:** Class B compressed stranded bare copper per ASTM B3 and B8
4. **Filler:** Paper filler (cable size 8 & 6 uses Polypropylene filler)
5. **Binder:** Polypropylene tape
6. **Armor:** ARMOR-X[®] Continuous Corrugated Welded Armor
7. **Overall Jacket:** Thermoplastic Solonon[®] Low Smoke Zero Halogen (LSZH-TP) Jacket

APPLICATIONS AND FEATURES:

Southwire's 600 Volt Type MC-HL ARMOR-X[®] power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, 250°C for short circuit conditions, and -50°C for cold bend. For uses in Class I, II, and III, Division 1 and 2 hazardous locations per NEC Article 501, 502, and 503. Cables with 3 ground wires suitable for VFD application.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- ICEA S-58-679 Control Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test





SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE® {UL} ARMOR-X® TYPE MC-HL 3/C XXX AWG (XX{mm2}) CU XHHW-2 GW 3 X X AWG 90°C SOLONON® JACKET -40°C ST1 SUN.RES. DIR. BUR. FOR CT USE 600V IEEE1202/FT4 -- VFD -- {NOM}-ANCE Tipo MC XHHW-2 CT FT4

Table 1 – Weights and Measurements

Cond. Size	Cond. Number	Strand Count	Diameter Over Conductor	Insul. Thickness	Ground	Dia. Over Armor	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
AWG/Kcmil		No. of Strands	inch	mil	No. x AWG	inch	mil	inch	lb/1000ft	lb/1000ft
350	3	37	0.661	65	3 x 6	2.200	60	2.320	3435	4623

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

Cond. Size	Cond. Number	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
AWG/Kcmil		inch	lb	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Amp	Amp
350	3	16.2	8400	0.031	0.039	0.012	0.040	310	350

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

