



# ETFE 200°C 600V UL 10086

Flexible UL/CSA Approved Lead Wire, Temp Rating 200°C



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Stranded tinned, annealed copper per ASTM B33
- Insulation:** Extruded ETFE fluoropolymer jacket

## APPLICATIONS AND FEATURES:

Used for wiring of electric heaters, appliances, thermocouples, gas igniters, electrical and electronic components, and other products up to 200°C.

Excellent chemical resistance, excellent resistance to fluids, excellent resistance to cut through and low coefficient of friction makes installation easier. Flexible. Good mechanical strength. Available in all colors.

## SPECIFICATIONS:

- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL AWM Appliance wire approvals as listed in Table 1
- RoHS-3 Complies with European Directive 2015/863

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft	Temp. Rating °C	Standard (UL or other) Style/Type
CZ066A	6	84	25	0.243	97	200	10086

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◊ Cable marked with this symbol is a standard stock item  
 Dimensions and weights for other cable configurations are available upon request.  
 \*NPC Conductor required for 200°C Rating

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mm	Approx. OD mm	Approx. Weight kg/km	Temp. Rating °C	Standard (UL or other) Style/Type
CZ066A	6	84	0.64	6.17	144	200	10086

