



PFA 250°C 600V UL 1727

Flexible UL/CSA Approved Lead Wire, Temp Rating 250°C




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Stranded annealed nickel plated copper
- Insulation:** Extruded PFA fluoropolymer

APPLICATIONS AND FEATURES:

Used for wiring of electric heaters, appliances, thermocouples, gas igniters, electrical and electronic components and other products that require a temperature rating up to 250° C.

Excellent chemical resistance, excellent resistance to fluids, and low coefficient of friction makes installation easier. Flexible. Good mechanical strength. Available in all colors.

SPECIFICATIONS:

- UL AWM Appliance wire approvals as listed in Table 1
- CSA AWM I A/B FT1
- RoHS-3 Complies with European Directive 2015/863

Table 1 – Weights and Measurements

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft	Temp. Rating °C	Standard (UL or other) Style/Type
CP206A	20	19/.0073	20	0.080	7	250	1727

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Dimensions and weights for other cable configurations are available upon request.

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mm	Approx. OD mm	Approx. Weight kg/km	Temp. Rating °C	Standard (UL or other) Style/Type
CP206A	20	19/.0073	0.51	2.03	10	250	1727

