



## Fire Alarm FPLP Solid Non-Shielded

300V, 75°C, Multi-Conductor, Unshielded, Solid Copper as FPLP. Minimum Temperature 0°C , Maximum Temperature 75°C



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Solid bare copper per ASTM B3
2. **Insulation:** Low Smoke Polyvinyl Chloride LS-PVC
3. **Rip Cord:** Rip cord for ease of jacket removal
4. **Jacket:** Low Smoke Polyvinyl Chloride LS-PVC, Color: RED

### APPLICATIONS AND FEATURES:

Fire protective signaling circuits. Also for smoke detectors, voice communications, audio control and initiating circuits. Article 760 of the NEC. For use in plenum spaces. Minimum Temperature 0°C , Maximum Temperature 75°C

### SPECIFICATIONS:

- UL 1424 Cables for Power-Limited Fire-Alarm Circuits
- UL 1424 Listed FPLP
- NFPA 70 NFPA 101, NFPA 130, and NFPA 502
- UL 13 Power-Limited Circuit Cables
- UL 444 Communications Cables (90°C, 300V)
- RoHS-2 (European Directive 2011/65/EU)

### SAMPLE PRINT LEGEND:

XX AWG X/C E75610 c{UL}US CMP/CL3P/FPLP 75°C -- CMP FT6 MADE IN USA ROHS-2 COMPLIANT -- {MM/DD/YY}  
{HH:MM} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET





**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance	Min Bending Radius	Allowable Ampacity 75°C	Allowable Ampacity 90°C
	AWG	No.	strands	inch	mil	mil	inch	lb / 1000ft	lb / 1000ft	Ω /1000ft	Ω /1000ft	Ω/1000ft	inch	Amp	Amp
18 AWG															
G40005-1	18	2	Solid	0.040	10	15	0.144	9	15	6.669	8.035	0.036	0.5	-	14
G40505-1	18	4	Solid	0.040	10	15	0.168	19	28	6.669	8.035	0.036	0.6	-	11
G40503-1	18	6	Solid	0.040	10	15	0.184	30	41	6.669	8.035	0.036	1.1	-	11
16 AWG															
G50032-1	16	2	Solid	0.050	10	15	0.164	15	22	4.181	5.037	0.033	0.6	-	18
G50370-1	16	4	Solid	0.050	10	15	0.196	31	41	4.181	5.037	0.033	0.7	-	14
14 AWG															
G60004-1	14	2	Solid	0.064	10	15	0.196	25	33	2.631	3.170	0.058	0.7	20	25
G60347-1	14	4	Solid	0.064	10	15	0.226	50	61	2.631	3.170	0.058	0.9	16	20
12 AWG															
G70009-1	12	2	Solid	0.080	10	15	0.226	39	49	1.662	2.002	0.054	0.9	25	30

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◇ Cable marked with this symbol is a standard stock item

