SIMpull® T90 Copper

SIMpull® THHN THWN-2 MTW / c(UL) T90 Nylon TWN75 Copper Conductor, 600V, Thermoplastic-Insulated Cable, All Sizes Rated TWN75




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid soft drawn copper per ASTM B3 or Combination unilay-stranded copper conductors per ASTM B3 and B787
2. **Insulation:** Colored Polyvinyl Chloride (PVC)
3. **Sheath:** Nylon sheath utilizing SIMpull® technology

APPLICATIONS AND FEATURES:

• SIMpull® THHN, THWN-2, and MTW (UL): Suitable for dry locations not exceeding 90°C. For Gasoline and Oil Resistant II applications not to exceed 75°C.
• MTW (UL): suitable for dry locations not exceeding 90°C. For wet locations, Gasoline and Oil Resistant II applications not to exceed 60°C.
• T90 Nylon c(UL): cables are primarily intended for installation in conduit (raceways) as exposed wiring in dry locations not exceeding 90°C.
• TWN75 c(UL): suitable for wet or dry locations at not more than 75°C.

The maximum voltage rating for all intended applications is 600 volts. Minimum installation handling temperature is limited to -25°C. Minimum operating temperature limited to -40°C. Non-SIMpull Silicone Free sizes 14, 12, and 10 AWG.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B787 19 Wire Combination Unilay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 758 Standard for Appliance Wiring Material
- UL 1063 Machine Tool Wiring (MTW)
- CSA Certified LL90458
- CSA C22.2 No. 75 Thermoplastic Insulated Wires and Cables
- Canadian Electrical Code
- CSA FT-1 Flame Test

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

SAMPLE PRINT LEGEND:

SOUTHWIRE SIMpull™ E51583 {UL} (XX AWG) XX.X{mm2} CU TYPE MTW OR THWN-2 OR THHN OR GASOLINE AND OIL RESISTANT II OR AWM 600 VOLTS VW-1 --- {CSA} T90 NYLON OR TWN75 600 VOLTS FT1 {NOM}-ANCE 90°C - (X AWG) --- RoHS PAT www.patentSW.com

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Insul. Thickness	Insulation Color	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/ Kcmil	No. of Strands	inch	mil		mil	inch	lb/1000ft	lb/1000ft
507665◊	14	SOLID	0.064	15	BK	5	0.106	12	16
507715◊	14	19	0.073	15	BN	5	0.113	13	16
495770◊	12	SOLID	0.08	15	BK	5	0.123	20	24
672667◊	12	19	0.09	15	BN	5	0.132	20	24
484626◊	10	SOLID	0.101	20	RD	5	0.154	31	37
472142◊	10	19	0.117	20	BE	5	0.165	32	39
472183◊	8	19	0.143	30	GN	5	0.217	51	63
472233◊	6	19	0.179	30	GN	5	0.253	81	95
677345◊	4	19	0.226	40	WE	5	0.324	129	154
677819◊	3	19	0.254	40	RD	5	0.352	162	190
672394◊	2	19	0.286	40	WE	5	0.384	205	236
677817◊	1/0	19	0.361	50	WE	8	0.48	326	373
688051◊	2/0	19	0.42	50	GN	5	0.524	411	464
471995◊	3/0	19	0.471	50	BK	5	0.574	518	576
677818◊	350	37	0.661	60	BK	9	0.783	1081	1176
684084◊	1	19	0.322	50	BK	8	0.441	258	301
677820◊	4/0	19	0.512	50	WE	8	0.63	655	721

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/ Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
507665◊	14	0.4	32	2.631	3.265	0.058	20	25
507715◊	14	0.5	32	2.631	3.265	0.058	20	25
495770◊	12	0.5	52	1.662	2.063	0.054	25	30
672667◊	12	0.5	52	1.662	2.063	0.054	25	30
484626◊	10	0.6	83	1.04	1.291	0.05	35	40
472142◊	10	0.7	83	1.04	1.291	0.05	35	40
472183◊	8	0.9	132	0.653	0.81	0.052	50	55
472233◊	6	1	209	0.411	0.51	0.051	65	75
677345◊	4	1.3	333	0.258	0.32	0.048	85	95
677819◊	3	1.4	420	0.205	0.254	0.047	100	115
672394◊	2	1.5	530	0.162	0.201	0.045	115	130
677817◊	1/0	1.9	844	0.102	0.127	0.044	150	170
688051◊	2/0	2.1	1064	0.082	0.102	0.043	175	195
471995◊	3/0	2.3	1342	0.064	0.079	0.042	200	225
677818◊	350	3.1	2800	0.031	0.039	0.04	310	350
684084◊	1	1.8	669	0.128	0.159	0.046	130	145
677820◊	4/0	2.5	1692	0.051	0.063	0.041	230	260

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.
* Ampacities have been adjusted for more than Three Current-Carrying Conductors.
* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
* Non-SIMpull Silicone Free sizes: 14, 12, and 10 AWG.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 3- Stock Code by Color

Cond. Size AWG	Stranding Num	Black	Red	White	Yellow	Orange	Blue	Brown	Green	White/Blue
14	1 (SOLID)	507665	507699	507673	507723	610483	507707	553096	507681	
14	19	472001	472027	472019	672659	687517	472043	507715	472035	678050
12	1 (SOLID)	495770	495796	495788	507657	507632	495812	507640	495804	
12	19	472050	472076	472068	672675	552660	472092	672667	472084	
10	1 (SOLID)	507731	484626	507749			507756		672683	
10	19	472100	472126	472118	552663	610486	472142	552662	472134	
8	19	472159	611462 or 472175	472167			472191		472183	
6	19	472209	472225	472217			472241		472233	
4	19	472258							472282	
3	19	484675		484667					684068	
2	19	672386		672394					684076	
1	19	684084								
1/0	19	471979								
2/0	19	672402							688051	
3/0	19	471995		471987						
4/0	19			677820						

Copyright © 2026 Southwire Company, LLC. All Rights Reserved