



MC-AP™ HCF Type MC All Purpose Health Care Facility THHN/THWN Circuit Size Copper Conductor 120/208V Colors Green Aluminum Armor

Copper THHN Insulated Conductors. Full-Size Aluminum Equipment Grounding/Bonding Conductor. UL Listed 600 Volt. Rated VW1. Lightweight Aluminum Interlocked Armor is Part of Equipment Bonding/Grounding Path.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid or 19 strands class C compressed copper per ASTM B3 and ASTM B8
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Binder:** Mylar tape
4. **Ground:** A Green insulated Polyvinyl Chloride with Nylon Sheath Type THHN/THWN ground. Redundant grounding provided by a bare 8000 series aluminum grounding/bonding conductor and armor.
5. **Armor:** Green Aluminum Interlocked Armor

APPLICATIONS AND FEATURES:

Southwire MC-AP HCF Type MC All Purpose Health Care Facility Cable is suitable for use as follows:

- Branch-circuit wiring for patient care areas of hospitals, medical centers, and other health care facilities (when installed in accordance with NEC® Articles 517 and 330, and mechanically protected per Article 300.4). Such areas include nursing homes, dental offices, clinics, and outpatient facilities. Use in hazardous anesthetizing areas is prohibited.
- Applications requiring redundant, dedicated or isolated grounding paths.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2)
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Use with UL Listed MCI-A fittings.
- Binder tape with print legend wrapped around assembly.
- Type THHN/THWN rated 90°C Dry.
- Armor is in contact with aluminum grounding/bonding conductor and serves as a redundant equipment grounding path component

Southwire Armorlite® Type MC Cable - meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)





- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- RoHS-2 (European Directive 2011/65/EU)
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

SOUTHWIRE E96627 {UL} TYPE MC XX AWG THHN OR THWN CDRS FOR USE IN CABLE TRAYS 600 VOLTS




Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Diameter Over Armor	Copper Weight	Overall Weight
	AWG/ Kcmil			inch		mils	No. x AWG	inch	lbs/ 1000ft	lbs/ 1000ft
14 AWG Solid										
5603890	14	2	BK,WE	0.064	Solid	20	1x14	0.468	37	87
5603920	14	3	BK,RD,WE	0.064	Solid	20	1x14	0.495	50	105
12 AWG Solid										
641246	12	2	BE,WE/BE,GN	0.08	Solid	20	1x10	0.512	59	118
641242	12	2	BK,WE/BK,GN	0.08	Solid	20	1x10	0.506	59	117
641244	12	2	RD,WE/RD,GN	0.08	Solid	20	1x10	0.512	59	118
559324	12	3	RD,BE,WE,GN	0.08	Solid	20	1x10	0.538	79	144
555280	12	3	BK,RD,WE,GN	0.08	Solid	20	1x10	0.538	79	144
559326	12	3	BK,BE,WE,GN	0.08	Solid	20	1x10	0.538	79	144
555281	12	4	BK,RD,BE,WE,GN	0.08	Solid	20	1x10	0.573	99	172
585713	12	4	BE,WE/BE,WE/RD,RD,GN	0.08	Solid	20	1x12	0.573	99	172
589380	12	4	BE,WE/BE,WE/BK,BK,GN	0.08	Solid	20	1x12	0.573	99	172
5593220	12	2	BE,WE	0.080	Solid	20	1x12	0.512	59	118
5593200	12	2	RD,WE	0.080	Solid	20	1x12	0.513	40	119
5552790	12	2	BK,WE	0.080	Solid	20	1x12	0.506	59	117
12 AWG 19 Strands										
558722	12	2	RD,WE,GN	0.088	19	20	1x10	0.528	60	122
556361	12	2	BK,WE,GN	0.088	19	20	1x10	0.534	60	123
558720	12	2	BE,WE,GN	0.088	19	20	1x10	0.528	60	122
556363	12	3	BK,WE,RD,GN	0.088	19	20	1x10	0.562	80	150
559361	12	4	BK,WE,RD,BE,GN	0.088	19	20	1x10	0.6	100	178
10 AWG Solid										
560836	10	2	RD,WE,GN	0.101	Solid	25	1x8	0.58	92	169
555282	10	2	BK,WE,GN	0.101	Solid	25	1x8	0.58	92	169
560838	10	2	BE,WE,GN	0.101	Solid	25	1x8	0.58	92	169
555283	10	3	BK,RD,WE,GN	0.101	Solid	25	1x8	0.619	123	210
555285	10	4	BK,RD,BE,WE,GN	0.101	Solid	25	1x8	0.663	154	251
674331	10	6	BK,RD,BE,BK/WE,RD/WE,BE/ WE,GN	0.101	Solid	25	1x8	0.709	216	329
644515	10	10	BK,RD,BE,BK/WT,RD/ BK,WT,WT/BK,WT/RD,WT/ BE,WT/YW,GN	0.101	Solid	25	1x10	0.913	340	526
586265	10	12	BK,RD,BE,BK/RD,RD/WT,BE/ RD,BK/YW,RD/YW,BE/ YW,WT,WT	0.101	Solid	25	1x10	0.909	402	589
10 AWG 19 Strands										
560798	10	2	BK,WE,GN	0.113	19	25	1x8	0.613	97	181
567242	10	6	BK,RD,BE,WE/BK,WE/RD,WE/ BE,GN	0.113	19	25	1x10	0.755	226	350
582217	10	8	BK,RD,BE,WE,BK/WE,WE/ BK,RD/WE,BE/WE,GN	0.113	19	25	1x10	0.908	291	479





Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Diameter Over Armor	Copper Weight	Overall Weight
	AWG/Kcmil			inch		mils	No. x AWG	inch	lbs/1000ft	lbs/1000ft
583947	8	2	BK,WE,GN	0.141	19	35	1x8	0.67	135	235
677635	8	2	BK,RD,GN	0.141	19	35	1x8	0.67	135	236
596687	8	6	BK,RD,BE,WE/BK,WE/RD,WE/BE,GN	0.141	19	35	1x8	0.949	360	572

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
Note: Conductor number = number of phase conductors plus neutral. Does not include green ground.
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.




Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
14 AWG Solid							
14	2	3.3	2.631	3.170	0.058	20	25
14	3	3.5	2.631	3.170	0.058	20	25
12 AWG Solid							
12	2	3.6	1.662	2.002	0.054	25	30
12	2	3.5	1.662	2.002	0.054	25	30
12	2	3.6	1.662	2.002	0.054	25	30
12	3	3.8	1.662	2.002	0.054	20	24
12	3	3.8	1.662	2.002	0.054	20	24
12	3	3.8	1.662	2.002	0.054	20	24
12	4	4	1.662	2.002	0.054	20	24
12	4	4	1.662	2.002	0.054	20	24
12	4	4	1.662	2.002	0.054	20	24
12	2	3.6	1.662	2.002	0.054	25	30
12	2	3.9	1.662	2.002	0.054	25	30
12	2	3.5	1.662	2.002	0.054	25	30
12 AWG 19 Strands							
12	2	3.7	1.662	2.002	0.054	25	30
12	2	3.7	1.662	2.002	0.054	25	30
12	2	3.7	1.662	2.002	0.054	25	30
12	3	3.9	1.662	2.002	0.054	20	24
12	4	4.2	1.662	2.002	0.054	20	24
10 AWG Solid							
10	2	4.1	1.04	1.253	0.05	35	40
10	2	4.1	1.04	1.253	0.05	35	40
10	2	4.1	1.04	1.253	0.05	35	40
10	3	4.3	1.04	1.253	0.05	28	32
10	4	4.6	1.04	1.253	0.05	28	32
10	6	5	1.04	1.253	0.05	28	32
10	10	6.4	1.04	1.253	0.05	17	20
10	12	6.4	1.04	1.253	0.05	17	20
10 AWG 19 Strands							
10	2	4.3	1.04	1.253	0.05	35	40
10	6	5.3	1.04	1.253	0.05	24	28
10	8	6.4	1.04	1.253	0.05	17	20
8	2	4.7	0.653	0.786	0.052	50	55
8	2	4.7	0.653	0.786	0.052	50	55
8	6	6.6	0.653	0.786	0.052	35	38

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections





310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

MCAP Savings Calculator

