300V SJTOOW Cord with PVC Jacket 105°C

300 Volt, 105°C Flexible Cord. Premium Oil Resistance, Sunlight, Water Resistance, and Flame Retardant. UL / CSA listed.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B3 and B174
2. **Insulation:** Moisture and oil resistant Polyvinyl Chloride (PVC)
3. **Filler:** Non-wicking polypropylene fillers, with a tissue-paper separator wrapped around the assembly
4. **Jacket:** Black Polyvinyl Chloride (PVC). Other colors available upon request.

APPLICATIONS AND FEATURES:

Southwire Type SJTOOW Flexible Cords are permitted for indoor and outdoor temporary power uses, portable industrial machinery, compressors, conveyor and automated production equipment. Cords are suitable for use in temperatures between -40°C to maximum 105°C.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 62 Flexible Cords and Cables
- CSA C22.2 No. 49 Flexible Cords and Cables
- Passes CSA FT2 Flame Test
- RoHS-3 Complies with European Directive 2015/863
- NEC Article 400 Flexible Cords, Cables and Fixture Wire
- Federal Specification J-C-580B

SAMPLE PRINT LEGEND:

SOUTHWIRE® XX AWG (X.XX{mm2}) X/C SJTOOW E46194 {UL} 300V -40°C TO 105°C -- CSA LL90458 SJTOOW 300V -40°C to 105°C FT2 WATER RESISTANT

PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	DC Resistance	Insul. Color	Jacket Color
	AWG/ Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp	Ω/1000ft		
588932!	16	3	26	30	35	0.329	69	10	4.181	BK,WE,GN	BK
677226	16	4	26	30	30	0.36	79	8	4.181	BK,WE,RD,GN	BK
564553!	14	3	41	30	35	0.365	91	15	2.621	BK,WE,GN	BK
560694!	14	3	41	30	30	0.375	93	15	2.621	BK,WE,GN/ YW	YW
560695	12	3	65	30	45	0.435	134	20	1.652	BK,WE,GN	YW
565687!	10	3	105	45	65	0.596	233	25	1.04	BK,WE,GN/ YW	BK

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.
! No paper filler

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	DC Resistance	Insul. Color	Jacket Color
	AWG/ Kcmil	No.	No.	mm	mm	mm	kg/km	Amp	Ω/km		
588932!	16	3	26	0.76	0.89	8.36	103	10	13.72	BK,WE,GN	BK
677226	16	4	26	0.76	0.76	9.14	118	8	13.72	BK,WE,RD,GN	BK
564553!	14	3	41	0.76	0.89	9.27	135	15	8.60	BK,WE,GN	BK
560694!	14	3	41	0.76	0.76	9.52	138	15	8.60	BK,WE,GN/ YW	YW
560695	12	3	65	0.76	1.14	11.05	199	20	5.42	BK,WE,GN	YW
565687!	10	3	105	1.14	1.65	15.14	347	25	3.41	BK,WE,GN/ YW	BK

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved