



## 1/C AL 1000V RWU90

Single 8000 Series Aluminum Conductor, 600V Alumaflex Strand, No. 6 AWG to 1000 Kcmil, FT4 Flame Test Rating - (in all colours, sizes 350 KCMIL & larger), 90°C MAX -40°C MIN, Sunlight Resistant



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800
2. **Insulation:** Cross Linked Polyethylene (XLPE)

### APPLICATIONS AND FEATURES:

Southwire's SIMpull® aluminum RWU90 is for open wiring used in raceways (except cabletroughs and ventilated flexible cableways) in dry or wet locations. For open wiring exposed to the weather. Minimum recommended installation temperature minus 40°C (with suitable handling procedures). Maximum conductor temperature 90°C.

### SPECIFICATIONS:

- ASTM B800 8000 Series Aluminum Alloy Wire
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 38 Thermoset-insulated wires and cables

### SAMPLE PRINT LEGEND:

{SQMTR} SOUTHWIRE® LL90458 {CSA} XX AWG/KCMIL (XX{mm<sup>2</sup>}) COMPACT AL. --- {ALUMAFLEX}® AA8176 RWU90 XLPE 1000 VOLTS -40°C SR





**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Strand	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C†
	AWG/Kcmil	No.	mil	inch	lb/1000ft	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp
568942◇	6	7	70	0.339	55	1.3	157	0.674	0.812	0.051	55
568943◇	4	7	70	0.383	76	1.5	250	0.424	0.51	0.048	75
568944◇	2	6	70	0.438	106	1.7	398	0.267	0.321	0.045	100
568945◇	1	18	95	0.499	130	1.9	502	0.211	0.254	0.046	115
568794◇	1/0	18	95	0.526	152	2.1	633	0.168	0.201	0.044	135
570875◇	2/0	12	95	0.576	187	2.3	798	0.133	0.16	0.043	150
570772◇	3/0	16	95	0.623	226	2.4	1006	0.105	0.126	0.042	175
568793◇	4/0	19	95	0.675	275	2.7	1269	0.084	0.1	0.041	205
568792◇	250	22	110	0.74	325	2.9	1500	0.071	0.086	0.041	230
568791◇	350	35	110	0.848	441	3.3	2100	0.05	0.062	0.04	280
568789◇	500	34	110	0.97	601	3.8	3000	0.035	0.044	0.039	350
593373◇	600	37	108	1.077	747	5.3	3600	0.029	0.037	0.039	385
568788◇	750	61	125	1.172	887	5.8	4500	0.024	0.031	0.038	435
604121◇	1000	58	125	1.324	1153	6.6	6000	0.018	0.025	0.037	500

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size	Strand	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C
	AWG/Kcmil	No.	mm	mm	kg/km	mm	newton	Ω/km	Ω/km	Ω/km	Amp
568942◇	6	7	1.78	8.61	82	33.02	699	2.21	2.66	0.1673	55
568943◇	4	7	1.78	9.73	113	38.10	1113	1.39	1.67	0.1575	75
568944◇	2	6	1.78	11.13	158	43.18	1771	0.88	1.05	0.1476	100
568945◇	1	18	2.41	12.67	193	48.26	2234	0.69	0.83	0.1509	115
568794◇	1/0	18	2.41	13.36	226	53.34	2817	0.55	0.66	0.1444	135
570875◇	2/0	12	2.41	14.63	278	58.42	3551	0.44	0.52	0.1411	150
570772◇	3/0	16	2.41	15.82	336	60.96	4477	0.34	0.41	0.1378	175
568793◇	4/0	19	2.41	17.15	409	68.58	5647	0.28	0.33	0.1345	205
568792◇	250	22	2.79	18.80	484	73.66	6675	0.23	0.28	0.1345	230
568791◇	350	35	2.79	21.54	656	83.82	9345	0.16	0.20	0.1312	280
568789◇	500	34	2.79	24.64	894	96.52	13350	0.11	0.14	0.1280	350
593373◇	600	37	2.74	27.36	1112	134.62	16020	0.10	0.12	0.1280	385
568788◇	750	61	3.18	29.77	1320	147.32	20025	0.08	0.10	0.1247	435
604121◇	1000	58	3.18	33.63	1716	167.64	26700	0.06	0.08	0.1214	500

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM

