



PFA 250°C 600V UL 1727

Flexible UL/CSA Approved Lead Wire, Temp Rating 250°C




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Stranded annealed nickel plated copper
2. **Insulation:** Extruded PFA fluoropolymer

APPLICATIONS AND FEATURES:

Used for wiring of electric heaters, appliances, thermocouples, gas igniters, electrical and electronic components and other products that require a temperature rating up to 250° C.

Excellent chemical resistance, excellent resistance to fluids, and low coefficient of friction makes installation easier. Flexible. Good mechanical strength. Available in all colors.

SPECIFICATIONS:

- UL AWM Appliance wire approvals as listed in Table 1
- CSA AWM I A/B FT1
- RoHS-3 Complies with European Directive 2015/863





Table 1 – Weights and Measurements

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft	Temp. Rating °C	Standard (UL or other) Style/Type
CP246A	24	7/.008	20	0.055	4	250	1727
CP226A	22	10/.0058	20	0.070	5	250	1727
CP206A	20	19/.0073	20	0.080	7	250	1727
CP186A	18	19/.0092	20	0.090	10	250	1727
CP166A	16	19/.0117	20	0.100	13	250	1727
CP146A	14	19/.0147	20	0.110	17	250	1727
CP126A	12	19/.0185	20	0.130	25	250	1727
CP106A	10	37/.0159	20	0.145	35	250	1727
CP086A	8	133/.0111	30	0.230	70	250	1727
CP066A	6	133/.0141	30	0.270	105	250	1727
CP046A	4	133/.0177	30	0.325	160	250	1727
CP026A	2	133/.0223	30	0.395	235	250	1727
CP016A	1	259/.0177	45	0.470	320	250	1727
CP1T6A	1/0	259/.0202	45	0.515	400	250	1727
CP2T6A	2/0	259/.0229	45	0.570	495	250	1727
CP3T6A	3/0	259/.0255	45	0.610	565	250	1727
CP4T6A	4/0	259/.0286	45	0.690	730	250	1727

All dimensions are nominal and subject to normal manufacturing tolerances
 ◇ Cable marked with this symbol is a standard stock item
 Dimensions and weights for other cable configurations are available upon request.

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mm	Approx. OD mm	Approx. Weight kg/km	Temp. Rating °C	Standard (UL or other) Style/Type
CP246A	24	7/.008	0.51	1.40	6	250	1727
CP226A	22	10/.0058	0.51	1.78	7	250	1727
CP206A	20	19/.0073	0.51	2.03	10	250	1727
CP186A	18	19/.0092	0.51	2.29	15	250	1727
CP166A	16	19/.0117	0.51	2.54	19	250	1727
CP146A	14	19/.0147	0.51	2.79	25	250	1727
CP126A	12	19/.0185	0.51	3.30	37	250	1727
CP106A	10	37/.0159	0.51	3.68	52	250	1727
CP086A	8	133/.0111	0.76	5.84	104	250	1727
CP066A	6	133/.0141	0.76	6.86	156	250	1727
CP046A	4	133/.0177	0.76	8.25	238	250	1727
CP026A	2	133/.0223	0.76	10.03	350	250	1727
CP016A	1	259/.0177	1.14	11.94	476	250	1727
CP1T6A	1/0	259/.0202	1.14	13.08	595	250	1727
CP2T6A	2/0	259/.0229	1.14	14.48	737	250	1727
CP3T6A	3/0	259/.0255	1.14	15.49	841	250	1727
CP4T6A	4/0	259/.0286	1.14	17.53	1086	250	1727

