



CU 600/1000V XLPE Insulation PVC Jacket XHHW-2. CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free

Type TC-ER Power Cable 600 or 1000 Volt Three Conductor Copper, Cross Linked Polyethylene (XLPE) insulation XHHW-2 Polyvinyl Chloride (PVC) Jacket with 1 Copper Ground (Bare or Insulated). CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Insulation:** Cross Linked Polyethylene (XLPE) Type XHHW-2
3. **Grounding Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8. (When present, cable conductor sizes 8 & 6 AWG have an insulated green ground)
4. **Filler:** Paper filler (cable size 8 & 6 uses Polypropylene filler)
5. **Binder:** Polyester flat thread binder tape for cable sizes larger than 2 AWG
6. **Overall Jacket:** Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 600 or 1000 Volt Type TC-ER power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10. Sunlight Resistant - For Direct Burial - Silicone Free

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test





SAMPLE PRINT LEGEND:

Bare Ground: {SQFTG} SOUTHWIRE® {UL} XX AWG (X.XX{mm²}) 3/C TYPE TC-ER XHHW-2 CDRS 90°C JACKET SUNLIGHT RESISTANT DIRECT BURIAL 600V or 1000V {NOM}-ANCE XHHW-2 CT FT4 SR 600V 90C

Green Ground: {SQFTG} SOUTHWIRE® {UL} XX AWG (X.XX{mm²}) CU 3/C TYPE TC-ER XHHW-2 CDRS GW 1 X X AWG CU GREEN INSULATED 90°C JACKET SUNLIGHT RESISTANT DIRECT BURIAL 600V or 1000V {NOM}-ANCE XHHW-2 CT FT4 SR 600V 90C

Table 1 – Weights and Measurements

| Stock Number | Cond. Size | Cond. Number | Strand Count | Diameter Over Conductor | Insul. Thickness | Ground | Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight |
|--------------|---------------|--------------|----------------|-------------------------|------------------|-----------|------------------|------------|---------------|----------------|
| | AWG/ Kcmil | | No. of Strands | inch | mil | No. x AWG | mil | inch | lb/1000ft | lb/1000ft |
| 555196◇ | 8 | 3 | 7 | 0.141 | 45 | - x - | 60 | 0.627 | 154 | 283 |
| 480590◇ | 8 | 3 | 7 | 0.141 | 45 | 1 x 10 GG | 60 | 0.688 | 186 | 327 |
| 555195 | 6 | 3 | 7 | 0.177 | 45 | - x - | 60 | 0.704 | 245 | 386 |
| 480608◇ | 6 | 3 | 7 | 0.177 | 45 | 1 x 8 GG | 60 | 0.782 | 297 | 466 |
| 480616◇ | 4 | 3 | 7 | 0.225 | 45 | 1 x 8 | 60 | 0.806 | 441 | 612 |
| 480624◇ | 2 | 3 | 7 | 0.282 | 45 | 1 x 6 | 80 | 0.982 | 702 | 927 |
| 480632◇ | 1 | 3 | 19 | 0.322 | 55 | 1 x 6 | 80 | 1.106 | 864 | 1142 |
| 480640◇ | 1/0 | 3 | 19 | 0.361 | 55 | 1 x 6 | 80 | 1.200 | 1069 | 1417 |
| 480657◇ | 2/0 | 3 | 19 | 0.405 | 55 | 1 x 6 | 80 | 1.295 | 1326 | 1723 |
| 480665◇ | 3/0 | 3 | 19 | 0.456 | 55 | 1 x 4 | 80 | 1.399 | 1699 | 2065 |
| 480673◇ | 4/0 | 3 | 19 | 0.512 | 55 | 1 x 4 | 80 | 1.494 | 2109 | 2502 |
| 480681◇ | 250 | 3 | 37 | 0.558 | 65 | 1 x 4 | 80 | 1.619 | 2469 | 2940 |
| 672206 | 350 | 3 | 37 | 0.661 | 65 | 1 x 1 | 115 | 1.897 | 3535 | 4322 |
| 480707◇ | 350 | 3 | 37 | 0.661 | 65 | 1 x 3 | 115 | 1.910 | 3438 | 4127 |
| 588013 | 350 | 3 | 37 | 0.661 | 65 | 1 x 3/0 | 115 | 2.093 | 3797 | 4602 |
| 480715 | 400 | 3 | 37 | 0.705 | 65 | 1 x 3 | 115 | 2.014 | 3906 | 4756 |
| 582435 | 500 | 3 | 37 | 0.789 | 65 | 1 x 2 GG | 110 | 2.155 | 4878 | 5805 |
| 480723◇ | 500 | 3 | 37 | 0.789 | 65 | 1 x 2 | 115 | 2.167 | 4884 | 5701 |
| 890148 | 500 | 3 | 37 | 0.789 | 65 | 1 x 1/0 | 115 | 2.167 | 5007 | 5929 |
| 583697 | 500 | 3 | 37 | 0.789 | 65 | 1 x 2/0 | 115 | 2.274 | 5092 | 6099 |
| 593173 | 600 | 3 | 61 | 0.865 | 80 | 1 x 3/0 | 115 | 2.417 | 6136 | 7286 |
| 665766 | 600 | 3 | 61 | 0.865 | 80 | 1 x 1/0 | 115 | 2.417 | 5942 | 7038 |
| 890388◇ | 600 | 3 | 61 | 0.865 | 80 | 1 x 2 | 115 | 2.417 | 5820 | 6812 |
| TBA◇ | 600 | 3 | 61 | 0.865 | 80 | 1 x 2 | 110 | 2.436 | 5814 | 6950 |
| 665768 | 600 | 3 | 61 | 0.865 | 80 | 1 x 400 | 115 | 2.503 | 6860 | 7994 |
| 672210 | 600 | 3 | 61 | 0.865 | 80 | 1 x 250 | 115 | 2.578 | 6392 | 7594 |
| 589359 | 750 | 3 | 61 | 0.968 | 80 | 1 x 4/0 | 115 | 2.631 | 7676 | 8996 |
| 554410 | 750 | 3 | 61 | 0.968 | 80 | 1 x 1 | 115 | 2.631 | 7277 | 8597 |

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

GG: Green Insulated Ground

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.



Table 2 – Electrical and Engineering Data

| Stock Number | Cond. Size | Cond. Number | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 75°C | Inductive Reactance @ 60Hz | Allowable Ampacity At 75°C | Allowable Ampacity At 90°C |
|--------------|---------------|--------------|--------------------|------------------|----------------------|----------------------|----------------------------|----------------------------|----------------------------|
| | AWG/ Kcmil | | inch | lb | Ω/1000ft | Ω/1000ft | Ω/1000ft | Amp | Amp |
| 555196◇ | 8 | 3 | 2.5 | 396 | 0.653 | 0.786 | 0.052 | 50 | 55 |
| 480590◇ | 8 | 3 | 2.8 | 396 | 0.653 | 0.786 | 0.052 | 50 | 55 |
| 555195 | 6 | 3 | 2.8 | 629 | 0.411 | 0.495 | 0.051 | 65 | 75 |
| 480608◇ | 6 | 3 | 3.1 | 629 | 0.411 | 0.495 | 0.051 | 65 | 75 |
| 480616◇ | 4 | 3 | 3.2 | 1001 | 0.258 | 0.310 | 0.048 | 85 | 95 |
| 480624◇ | 2 | 3 | 3.9 | 1592 | 0.162 | 0.195 | 0.045 | 115 | 130 |
| 480632◇ | 1 | 3 | 5.5 | 2008 | 0.128 | 0.154 | 0.046 | 130 | 145 |
| 480640◇ | 1/0 | 3 | 6.0 | 2534 | 0.102 | 0.122 | 0.044 | 150 | 170 |
| 480657◇ | 2/0 | 3 | 6.5 | 3194 | 0.081 | 0.097 | 0.043 | 175 | 195 |
| 480665◇ | 3/0 | 3 | 7.0 | 4027 | 0.064 | 0.078 | 0.042 | 200 | 225 |
| 480673◇ | 4/0 | 3 | 7.5 | 5078 | 0.051 | 0.062 | 0.041 | 230 | 260 |
| 480681◇ | 250 | 3 | 8.1 | 6000 | 0.043 | 0.053 | 0.041 | 255 | 290 |
| 672206 | 350 | 3 | 9.5 | 8400 | 0.031 | 0.039 | 0.040 | 310 | 350 |
| 480707◇ | 350 | 3 | 9.6 | 8400 | 0.031 | 0.039 | 0.040 | 310 | 350 |
| 588013 | 350 | 3 | 12.6 | 8400 | 0.031 | 0.039 | 0.040 | 310 | 350 |
| 480715 | 400 | 3 | 12.1 | 9600 | 0.027 | 0.035 | 0.040 | 335 | 380 |
| 582435 | 500 | 3 | 12.9 | 12000 | 0.022 | 0.029 | 0.039 | 380 | 430 |
| 480723◇ | 500 | 3 | 13.0 | 12000 | 0.022 | 0.029 | 0.039 | 380 | 430 |
| 890148 | 500 | 3 | 13.0 | 12000 | 0.022 | 0.029 | 0.039 | 380 | 430 |
| 583697 | 500 | 3 | 13.6 | 12000 | 0.022 | 0.029 | 0.039 | 380 | 430 |
| 593173 | 600 | 3 | 14.5 | 14400 | 0.018 | 0.025 | 0.039 | 420 | 475 |
| 665766 | 600 | 3 | 14.5 | 14400 | 0.018 | 0.025 | 0.039 | 420 | 475 |
| 890388◇ | 600 | 3 | 14.5 | 14400 | 0.018 | 0.025 | 0.039 | 420 | 475 |
| TBA◇ | 600 | 3 | 14.6 | 14400 | 0.018 | 0.025 | 0.039 | 420 | 475 |
| 665768 | 600 | 3 | 15.0 | 14400 | 0.018 | 0.025 | 0.039 | 420 | 475 |
| 672210 | 600 | 3 | 15.5 | 14400 | 0.018 | 0.025 | 0.039 | 420 | 475 |
| 589359 | 750 | 3 | 15.8 | 18000 | 0.014 | 0.022 | 0.038 | 475 | 535 |
| 554410 | 750 | 3 | 15.8 | 18000 | 0.014 | 0.022 | 0.038 | 475 | 535 |

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

