



CU Compressed 5kV XLPE Insulation Airport Lighting

5000 Volt Non-Shielded Airport Lighting Cable, Copper Conductor With Cross-Linked Polyethylene Insulation XLPE. Meets (FAA) specification L-824 C For Underground Electrical Cable for Airport Lighting Circuits. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B copper per ASTM B3 and B8
2. **Insulation:** Cross-Linked Polyethylene (XLPE). Optional colors available upon request (green, blue, red, etc.)

APPLICATIONS AND FEATURES:

Southwire's Airport Lighting Cable meets the requirements of (FAA) L-824 C underground electrical cable for airport lighting circuits (AC 150/5345-53D), (AC 150/5345-7F). Southwire's Airport Lighting Cable is available in sizes #8 AWG through #4 AWG 7 strands. The conductors are bare annealed copper class B and covered with an abrasion, moisture, and heat resistant Cross-Linked Polyethylene XLPE insulation. The 5KV non-shielded cable is available in Black, Red and Yellow colors. Southwire Airport Lighting Cable is primarily used for series lighting circuits for runways, control systems, and other multi-purpose installations. It can be used in direct burial, conduit, or raceways. These cables are capable of operating continuously at a conductor temperature not in excess of 90°C for normal operation, 130°C for emergency and 250°C for short circuit conditions. Silicone Free.

- Cable is manufactured by Southwire Company in either Starkville, MS or Douglas, GA USA
- Cable has a warranty of 1 year from date of installation or 2 years from date of shipment whichever comes first.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-96-659 (NEMA WC 71) 2001-5000 V Nonshielded Cables
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- FAA L-824 C Specification Approved by (AC 150/5345-53D), (AC 150/5345-7F)

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE X AWG 5000V XLPE 90{D}C FAA-L824, TYPE C



**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size AWG/kcmil	Strand Count No. of Strands	Diameter Over Conductor inch	Insul. Thickness mil	Jacket Color	Approx. OD inch	Approx. Weight lb/1000ft
551529	8	7	0.141	110	BK	0.375	89
578009	8	7	0.141	110	RD/OE	0.375	89
669598	8	7	0.141	110	BE	0.375	89
669598	8	7	0.141	110	YW	0.375	89
551528	6	7	0.177	110	BK	0.415	125
587172	6	7	0.177	110	RD	0.415	125
551527	4	7	0.225	110	BK	0.460	180

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

