



CU Compressed 15kV NLEPR Insulation 100% IL Black CPE-TP Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Single Conductor Copper, 175 Mil No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level, Tape Shield, Thermoplastic Chlorinated Polyethylene (CPE-TP) Jacket, Dual Rated UL/CSA. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 175 Mil No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Thermoplastic Chlorinated Polyethylene (CPE-TP)

APPLICATIONS AND FEATURES:

Southwire's 15KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend when UL listed. Rated at -25°C for cold bend and cold impact and marked with "LTDD" when CSA listed or dual UL/CSA listed. Rated for 1000 lbs./FT maximum sidewall pressure. CT rated 1/0 and larger.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No.230 Tray Cables - Rated TC
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)





- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE® POWER CABLE {UL} XX KCMIL CU 175 MILS NL-EPR CPE JKT 15KV 100% INS LEVEL 25%TS TYPE MV-105 SUN RES DIR BUR OIL RES I/II {NESC}

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size*
	AWG/Kcmil	No. of Strands	inch	inch	inch	mil	inch	lb/1000ft	lb/1000ft	lb	inch	inch
TBA	2	7	0.282	0.670	0.730	80	0.910	218	532	530	10.9	2.5
TBA	1	19	0.322	0.710	0.770	80	0.950	273	608	669	11.4	3.0
TBA	1/0	19	0.361	0.749	0.809	80	0.989	341	696	844	11.8	3.0
TBA	2/0	19	0.405	0.793	0.853	80	1.033	427	805	1064	12.3	3.0
TBA	3/0	19	0.456	0.844	0.904	80	1.084	536	941	1342	13.0	3.0
TBA	4/0	19	0.512	0.900	0.960	80	1.140	672	1105	1692	13.6	3.5
TBA	250	37	0.558	0.954	1.014	80	1.194	791	1258	2000	14.3	3.5
TBA	300	37	0.611	1.006	1.066	80	1.246	1012	1506	2400	14.9	3.5
678579 [^]	350	37	0.661	1.037	1.097	80	1.277	1169	1670	2800	15.3	3.5
TBA	350	37	0.661	1.057	1.117	80	1.297	1103	1623	2800	15.5	4.0
586466	500	37	0.789	1.162	1.222	80	1.402	1641	2208	4000	16.8	4.0
TBA	600	61	0.865	1.271	1.331	80	1.511	1879	2518	4800	18.1	4.5
TBA	750	61	0.968	1.374	1.434	80	1.614	2344	3040	6000	19.3	4.5
TBA	1000	61	1.117	1.523	1.583	110	1.823	3119	4001	8000	21.8	5.0

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Conduit size based on 3 phase 40% fill-factor without ground

[^] Tinned copper tape shield





Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.204	0.044	0.049	0.575 + j0.458	0.204 + j0.05	2292	155/165	195/215
1	0.128	0.162	0.041	0.047	0.533 + j0.437	0.162 + j0.047	2416	175/185	225/250
1/0	0.102	0.128	0.037	0.045	0.499 + j0.418	0.128 + j0.045	2537	200/215	260/290
2/0	0.081	0.102	0.035	0.043	0.472 + j0.399	0.102 + j0.043	2673	230/245	300/335
3/0	0.064	0.081	0.032	0.042	0.449 + j0.377	0.082 + j0.042	2831	260/275	345/385
4/0	0.051	0.065	0.029	0.040	0.43 + j0.356	0.066 + j0.04	3005	295/315	400/445
250	0.043	0.056	0.027	0.039	0.417 + j0.336	0.057 + j0.039	3172	325/345	445/495
300	0.035	0.047	0.027	0.038	0.404 + j0.319	0.047 + j0.039	3057	357 ¹ /380 ¹	497 ¹ /552 ¹
350	0.031	0.041	0.024	0.037	0.394 + j0.303	0.042 + j0.037	3491	390/415	550/610
350	0.031	0.041	0.024	0.037	0.394 + j0.303	0.042 + j0.037	3491	390/415	550/610
500	0.022	0.030	0.021	0.035	0.372 + j0.268	0.031 + j0.035	3888	465/500	685/765
600	0.018	0.026	0.020	0.034	0.36 + j0.247	0.027 + j0.034	4154	505/544	765/855
750	0.014	0.023	0.018	0.033	0.346 + j0.225	0.024 + j0.033	4473	565/610	885/990
1000	0.011	0.019	0.016	0.033	0.327 + j0.198	0.02 + j0.033	4935	640/690	1060/1185

* Ampacities are based on:

* For Duct: Table 310.60(C)(77) Detail 1.

* For Free Air: Table 310.60(C)(69).

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

* Capacitive Reactance is between Phase-to-Shield.

¹ Linearly interpolated value

