



Armorlite® Type MC THHN/THWN PVC Jacketed Aluminum Conductor Feeder Cable 277/480V Colors

Aluminum THHN/THWN Insulated Singles with 8000 series Triple E™ Aluminum Alloy. Bare AlumaFlex™ Aluminum Alloy Grounding Conductor. UL Listed. 600 Volts. Rated VW-1. Lightweight Aluminum Interlocked Armor. Overall PVC Jacket. Sunlight Resistant.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B801
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Ground:** Bare aluminum ground
4. **Filler:** Fillers as needed
5. **Binder:** Mylar tape
6. **Armor:** Aluminum Interlocked Armor
7. **Jacket:** Polyvinyl Chloride (PVC) sunlight resistant, and corrosion resistant

APPLICATIONS AND FEATURES:

Southwire Armorlite® Type MC Feeder cable is suitable for use as follows:

- Feeder and service power distribution in commercial, industrial, institutional, and multi- residential buildings.
- Where exposed to cinder fills, strong chlorides, caustic alkalis, or vapors of chlorine or of hydrochloric acids.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Suitable for Wet Location per NEC 330.10(A)(11)
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways, or as aerial cable on a messenger.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(E)
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Type THHN/THWN rated 90°C Dry/ 75°C Wet

Southwire Armorlite® Type MC Feeder Cable - meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

Color Code

- 3/C: Brown, Orange, Yellow





- 4/C: Brown, Orange, Yellow, Gray

SPECIFICATIONS:

- ASTM B800 8000 Series Aluminum Alloy Wire
- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

SOUTHWIRE {UL} E96627 X/C XXX KCMIL COMPACT 8000 AL. --- TRIPLE E ALLOY AA8176 THHN OR THWN CDRS 600 VOLTS GW 1 X X AWG TYPE MC EZ-JKT FOR CT USE SUN. RES. 90 DEGREES C





Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Diameter Over Armor	Jacket Thickness	Approx. OD	Overall Weight
	AWG/ Kcmil			inch		mils	No. x AWG	inch	mil	inch	lbs/1000ft
587518◇	300	3	BN/OE/ GY	0.569	21	70	1x1	1.843	65	1.975	1717
584969◇	350	3	BN/OE/ YW	0.615	35	70	1x1	1.942	65	2.074	1910
587515◇	400	3	BN/OE/ GY	0.659	35	70	1x1	2.035	65	2.167	2098
591435◇	400	3	BN/OE/ YW	0.659	35	70	1x3/0	2.096	60	2.216	2169
677834◇	400	3	BN/OE/ YW	0.659	35	70	1x1 GG	2.088	65	2.220	2141
584970◇	500	3	BN/OE/ GY	0.735	35	70	1x1	2.201	65	2.333	2466
591438◇	600	3	BN/OE/ YW	0.812	58	80	1x3/0	2.415	75	2.565	3012
563305◇	750	3	BN/OE/ YW	0.908	53	80	1x750	2.895	75	3.045	4327
677814◇	1	4	BN/OE/ YW/GY	0.298	8	60	1x4 GG	1.333	50	1.433	834
560757◇	3/0	4	BN/OE/ YW/GY	0.422	16	60	1x4	1.614	60	1.734	1325
560758◇	4/0	4	BN/OE/ YW/GY	0.474	19	60	1x2	1.739	60	1.859	1576
560759◇	250	4	BN/OE/ YW/GY	0.520	22	70	1x1	1.901	65	2.033	1928
560760◇	300	4	BN/OE/ YW/GY	0.569	35	70	1x1	2.022	60	2.142	2105
560766◇	350	4	BN/OE/ YW/GY	0.615	35	70	1x1/0	2.133	65	2.265	2462
560767◇	500	4	BN/OE/ YW/GY	0.735	34	70	1x3/0	2.423	80	2.589	3348
560770◇	600	4	BN/OE/ YW/GY	0.812	41	80	1x3/0	2.642	80	2.808	3943
560784◇	750	4	BN/OE/ YW/GY	0.908	53	80	1x3/0	2.891	80	3.057	4682

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM





Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	Max Pull Tension	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/ Kcmil		Inches	Lbs	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
300	3	13.8	5400	0.059	0.071	0.041	230	260
350	3	14.5	6300	0.050	0.062	0.040	250	280
400	3	15.2	7200	0.044	0.054	0.040	270	305
400	3	15.5	7200	0.044	0.054	0.040	270	305
400	3	15.5	7200	0.044	0.054	0.040	270	305
500	3	16.3	9000	0.035	0.044	0.039	310	350
600	3	18.0	10800	0.029	0.037	0.039	340	385
750	3	21.3	13500	0.024	0.031	0.038	385	435
1	4	10.0	1606	0.211	0.254	0.046	80	92
3/0	4	12.1	3221	0.105	0.126	0.042	124	140
4/0	4	13.0	4062	0.084	0.100	0.041	144	164
250	4	14.2	4800	0.071	0.086	0.041	164	184
300	4	15.0	5760	0.059	0.071	0.041	184	208
350	4	15.9	6720	0.050	0.062	0.040	200	224
500	4	18.1	9600	0.035	0.044	0.039	248	280
600	4	19.7	11520	0.029	0.037	0.039	272	308
750	4	21.4	14400	0.024	0.031	0.038	308	348

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

