



CU 600V Royal® Bus Drop Cable

600 Volt. 60°C PVC Insulation and Jacket. Outdoor Rated.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class C stranded bare copper per ASTM B8
2. **Insulation:** Polyvinyl Chloride (PVC)
Color Code: 3/C Black, White, Red; 4/C Black, White, Red, Blue
3. **Grounding Conductor:** Class K stranded bare copper per ASTM B174
4. **Filler:** Polypropylene fillers as necessary for a round assembly
5. **Binder:** Tissue Paper
6. **Overall Jacket:** Gray, Polyvinyl Chloride (PVC) Jacket.

APPLICATIONS AND FEATURES:

Southwire Bus Drop Cable is suitable for use as branches from busways per the National Electrical Code® and for the connection of stationary equipment to facilitate the relocation of equipment.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 509 Bus Drop Cable

SAMPLE PRINT LEGEND:

SOUTHWIRE(R) ROYAL(R) E357438 14-3 BUS DROP CABLE TW INS. 600V (UL) 60C OUTDOOR




Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Strand Count	Diameter Over Conductor	Insul. Thickness	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Jacket Color
	AWG/Kcmil		No. of Strands	inch	mil	No. x AWG	mil	inch	lb/1000ft	lb/1000ft	
552123	14	3	19	0.073	30	3 x 18	45	0.379	53	101	Gray
552124	12	3	19	0.090	30	3 x 16	45	0.420	84	141	Gray
570109	12	4	19	0.090	20	4 x 18	45	0.411	102	150	Gray
552126	10	3	19	0.117	30	3 x 14	45	0.470	135	203	Gray
570110	10	4	19	0.117	30	4 x 16	45	0.491	159	223	Gray
552127	8	3	19	0.143	45	3 x 14	60	0.630	182	307	Gray
552128	6	3	19	0.179	60	3 x 14	60	0.794	284	479	Gray
552129	4	3	19	0.226	60	3 x 12	80	0.939	450	746	Gray
552130	2	3	19	0.286	60	3 x 12	80	1.071	681	998	Gray

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Cond. Number	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/Kcmil		inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
552123	14	3	1.5	98	2.631	3.170	0.058	20	25
552124	12	3	1.6	156	1.662	2.002	0.054	25	30
570109	12	4	1.6	156	1.662	2.002	0.054	20	24
552126	10	3	1.8	249	1.040	1.253	0.050	35	40
570110	10	4	1.9	332	1.040	1.253	0.050	28	32
552127	8	3	2.5	396	0.653	0.786	0.052	50	55
552128	6	3	3.1	629	0.411	0.495	0.051	65	75
552129	4	3	3.7	1001	0.258	0.310	0.048	85	95
552130	2	3	5.3	1592	0.162	0.195	0.045	115	130

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

