

Southwire® Machine Flex® CU 600/1000V THHN Insulation Black TPE Jacket. Silicone-Free

Type TC-ER Machine Tray Power Cable 600/1000 Volt Copper Conductors, Polyvinyl Chloride (PVC) with nylon layer Insulation Thermoplastic Elastomer Jacket, 90°C Dry 75°C Wet -40°C Cold Impact Identification Method 4. Silicone-Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K or I flexible stranded bare annealed copper per ASTM B3, B172, and B174
2. **Insulation:** Polyvinyl Chloride (PVC) with nylon layer Type THHN
3. **Ground:** One Green Ground with Yellow Stripe Type THHN
4. **Jacket:** Black Thermoplastic Elastomer (TPE) (other jacket colors available upon request)

APPLICATIONS AND FEATURES:

Southwire's Machine Flex® tray power cables 600/1000 Volt conform to NFPA 79 and are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial and where superior electrical properties are desired. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC® 336.10. These cables are capable of operating continuously at the conductor temperature not in excess of 75°C in wet locations and 90°C in dry locations, 130°C for emergency overload, and 150°C for short circuit conditions. For uses in Class I, II, Division 2 hazardous locations per NEC® Article 501 and 502. Southwire's machine tray cable is ideal to power CNC machines, grinding, cutting, metal forming, buffing, bottling equipment, conveyors, processing & packaging equipment, assembly lines, control panels, food and beverage, oil sands, plant expansion, wind energy and data centers. Multiple approvals for multiple applications. Cable is rated for -40°C cold impact. Two conductor cables contain no green/yellow ground.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 13 Power-Limited Circuit Cables
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 758 AWM Style 2587
- UL 1277 TC-ER
- UL 1690 Data Processing Cable (DP-1)
- UL 2250 Instrumentation Tray Cable
- UL 2277 Type WTTC
- CSA C22.2 No. 210 Appliance wiring material products I/II A/B (Sizes 16 - 8AWG)
- CSA C22.2 No.230 Tray Cables - Rated TC





- CSA C22.2 No. 239 Control and instrumentation cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Exceeds Ecolab PM-40-1 Material Resistance Test With 30-day Exposure, UL Verified V747862
- **CE/RoHS-2 – The CE Marking has been applied solely to express the conformance to the material restrictions identified in the RoHS-2 (2011/65/EU) Directive**
- NFPA 79 Electrical Standard for Industrial Machinery
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

SOUTHWIRE® XX AWG (X.XXmm²) X/C PVC/NYLON TYPE TC-ER E75755 (UL) 600V 90°C DRY 75°C WET SUN RES OIL RES I/II DIR BUR -40°C OR MTW FLEXING OR DP-1 OR WTTC 1000V OR PLTC OR ITC OR AWM 2587 -- LL90458 CSA CIC/TC FT4 OR AWM I/II A/B 105°C 1000V -40°C FT4 -- {NOM}-ANCE PLTC -- {CE} RoHS-2 MADE IN USA



Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	AC Resistance @ 75°C	Inductive Reactance	Min Bending Radius	Allowable Ampacity 75°C	Allowable Ampacity 90°C	Jacket Color
	AWG	No.	strands	inch	mil	No. x AWG	mil	inch	lb / 1000ft	lb / 1000ft	Ω /1000ft	Ω/1000ft	inch	Amp	Amp	
10 AWG																
TBA	10	3	105	0.117	25	1 x 10	45	0.511	128	200	1.253	0.050	2.0	35	40	Black
8 AWG																
653672	8	3	168	0.153	30	1 x 8	65	0.627	157	316	0.861	0.052	2.5	50	55	Black
677323◇	8	4	168	0.153	30	1 x 8	65	0.700	210	375	0.861	0.052	2.8	40	44	Black
653007	8	5	168	0.153	30	1 x 8	65	0.766	263	451	0.861	0.052	3.0	40	44	Black
6 AWG																
677324◇	6	4	259	0.198	30	1 x 6	65	0.817	358	564	0.541	0.051	3.2	52	60	Black
4 AWG																
677325◇	4	4	420	0.235	40	1 x 4	80	0.969	532	832	0.340	0.048	3.8	68	76	Black
2 AWG																
652968	2	3	651	0.302	40	1 x 2	100	1.064	637	987	0.216	0.045	5.3	115	130	Black
677326◇	2	4	651	0.302	40	1 x 2	100	1.196	849	1267	0.216	0.045	5.9	92	104	Black
516331	1	5	836	0.351	60	1 x 1	85	1.382	1313	1761	0.167	0.046	6.9	104	116	Black
674298	1/0	3	1064	0.354	60	1 x 2	80	1.318	1230	1694	0.126	0.044	6.6	150	170	Black
674300	2/0	3	1330	0.400	60	1 x 2	80	1.418	1485	2021	0.101	0.043	7.1	175	195	Black
TBA	3/0	3	1666	0.533	60	1 x 4	80	1.585	1748	2269	0.081	0.042	7.9	200	225	Black
TBA	4/0	3	2109	0.550	60	1 x 4	80	1.622	2175	2713	0.065	0.041	8.1	230	260	Black
TBA	250	3	2499	0.682	70	1 x 4	110	2.010	2556	3399	0.055	0.041	12.1	255	290	Black
677573	350	3	893	0.809	70	1 x 2	110	2.019	3497	4461	0.041	0.040	12.1	310	350	Black
458731	500	3	1221	0.858	70	1 x 1	110	2.388	4850	5934	0.03	0.039	14.3	380	430	Black
TBA	400	3	3990	0.878	70	1 x 3	110	2.434	4067	5159	0.036	0.040	14.6	335	380	Black
677576	600	3	1480	1.125	80	1 x 2	140	2.709	5841	7207	0.026	0.039	16.3	420	475	Black

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

