



# 35kV AL 100% TRXLPE Full Neutral (Based on Short Circuit) HI-DRI-PLUS® Renewable (Solar or Wind)

Moisture Blocked Aluminum Conductors. TRXLPE Insulation. Full Copper Concentric Neutrals. XLPE Jacket



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Moisture Blocked 1350 H16/H26 Aluminum, Class B Compressed or Compressed Unilay Stranded
2. **Strand Shield:** Semi-conducting Crosslinked Polyethylene
3. **Insulation:** Tree Retardant Crosslinked Polyethylene (TRXLPE)
4. **Insulation Shield:** Strippable Semi-conducting Crosslinked Polyethylene
5. **Concentric Neutral:** Annealed Copper Wires Helically Applied Full Concentric Neutral
6. **Overall Jacket & Water Block:** HI-DRI-PLUS® Water Swellable Powder Black Crosslinked Polyethylene (XLPE) with Red Extruded Stripes

## APPLICATIONS AND FEATURES:

- Predominately used for renewable projects with wind or solar applications.
- Suitable for use in wet or dry locations, direct burial, underground ducts, and exposure to direct sunlight.
- To be used at conductor temperature not to exceed 105°C normal operation.
- UL listed MV-105
- The concentric neutral counts and sizes listed in Table 1 are based on the ICEA P-45-482 short circuit calculation of an MV-90 design. The short circuit value in Table 1 is calculated using a higher thermal limit of a crosslinked XLPE jacket MV-105 design.

## SPECIFICATIONS:

- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B609 Standard Specification for Aluminum 1350 Round Wire, Annealed and Intermediate Tempers, for Electrical Purposes
- UL 1072 Medium-Voltage Power Cables
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661



**SAMPLE PRINT LEGEND:**

{SQFTG} SOUTHWIRE(R) HI-DRI-PLUS(R) (UL) XXX AWG AL 345 MILS TRXLPE TYPE MV-105 35KV 100% INSUL LEVEL -- (NESC) -- SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
629793	3/0 (19)	0.443	1.163	345	1.273	18x14	0.146	50	1.501	1052	12.0	1006
662956	4/0 (19)	0.498	1.218	345	1.328	14x12	0.118	50	1.589	1217	12.7	1269
456400	4/0 (19)	0.498	1.218	345	1.328	15x12	0.110	50	1.589	1236	12.7	1269
607596	4/0 (19)	0.498	1.218	345	1.328	23x14	0.114	75	1.610	1247	12.9	1269
TBA	250 (37)	0.558	1.294	345	1.404	27x14	0.097	75	1.682	1508	13.5	1500
TBA	350 (37)	0.661	1.397	345	1.507	24x12	0.069	75	1.819	1827	14.6	2100

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

\* Pulling tension based on pulling eye directly connected to conductor

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
3/0 (19)	0.105	0.132	0.060	0.050	0.336	2.0	0.186 + j0.739	0.132 + j0.050	9311	210	250
4/0 (19)	0.084	0.105	0.055	0.048	0.361	2.2	0.159 + j0.733	0.105 + j0.049	11506	240	280
4/0 (19)	0.084	0.105	0.055	0.048	0.361	2.188	0.159 + j0.734	0.105 + j0.049	12328	240	280
4/0 (19)	0.084	0.105	0.055	0.049	0.361	2.2	0.159 + j0.735	0.105 + j0.049	11898	240	280
250 (37)	0.071	0.090	0.051	0.047	0.389	2.4	0.144 + j0.729	0.090 + j0.048	13967	261	302
350 (37)	0.050	0.065	0.046	0.045	0.435	2.6	0.119 + j0.722	0.065 + j0.046	19725	315	365

\*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

\*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

\*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.



**Table 3 – Weights and Measurements (Metric)**

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
629793	3/0 (19)	11.25	29.54	8.76	32.33	18x14	0.48	1.27	38.13	1566	304.80	4477
662956	4/0 (19)	12.65	30.94	8.76	33.73	14x12	0.39	1.27	40.36	1811	322.58	5647
456400	4/0 (19)	12.65	30.94	8.76	33.73	15x12	0.36	1.27	40.36	1839	322.58	5647
607596	4/0 (19)	12.65	30.94	8.76	33.73	23x14	0.37	1.91	40.89	1856	327.66	5647
TBA	250 (37)	14.17	32.87	8.76	35.66	27x14	0.32	1.91	42.72	2244	342.90	6675
TBA	350 (37)	16.79	35.48	8.76	38.28	24x12	0.23	1.91	46.20	2719	370.84	9345

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Pulling tension based on pulling eye directly connected to conductor

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 4 – Electrical and Engineering Data (Metric)**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
3/0 (19)	0.3445	0.43	0.0183	0.1640	1.102	6.5617	0.186 + j0.739	0.132 + j0.050	9311	210	250
4/0 (19)	0.2756	0.34	0.0168	0.1575	1.184	7.2178	0.159 + j0.733	0.105 + j0.049	11506	240	280
4/0 (19)	0.2756	0.34	0.0168	0.1575	1.184	7.1785	0.159 + j0.734	0.105 + j0.049	12328	240	280
4/0 (19)	0.2756	0.34	0.0168	0.1608	1.184	7.2178	0.159 + j0.735	0.105 + j0.049	11898	240	280
250 (37)	0.2329	0.30	0.0155	0.1542	1.276	7.8740	0.144 + j0.729	0.090 + j0.048	13967	261	302
350 (37)	0.1640	0.21	0.0140	0.1476	1.427	8.5302	0.119 + j0.722	0.065 + j0.046	19725	315	365

\*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

\*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

\*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

CN  
Calculator

