

## 28kV CU 133% EPR (EAM) One-Third Neutral LLDPE

Single Conductor, 345 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM), 133% Insulation Level, One-third Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Conductor moisture block optional and tinned copper per ASTM B33 optional)
- Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
- Insulation:** 345 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM) 133% insulation level
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Concentric Neutral:** Helically applied soft drawn bare copper one-third concentric neutral
- Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

### APPLICATIONS AND FEATURES:

Southwire's 28kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

### SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 28000 VOLTS EPR INSULATION 345 MILS -- (NESC) --  
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET



**Table 1 – Weights and Measurements**

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
1 (Solid)	0.289	1.017	345	1.127	7x14	0.375	50	1.355	963	10.8	669
1 (19)	0.322	1.050	345	1.160	7x14	0.375	50	1.388	989	11.1	669
1/0 (Solid)	0.324	1.052	345	1.162	9x14	0.292	50	1.390	1084	11.1	844
1/0 (19)	0.361	1.089	345	1.199	9x14	0.292	50	1.427	1114	11.4	844
2/0 (19)	0.405	1.133	345	1.243	11x14	0.239	50	1.471	1260	11.8	1064
3/0 (19)	0.456	1.184	345	1.294	14x14	0.187	50	1.522	1448	12.2	1342
4/0 (19)	0.512	1.240	345	1.350	18x14	0.146	50	1.578	1682	12.6	1692
250 (37)	0.558	1.294	345	1.404	21x14	0.125	75	1.682	1967	13.5	2000
350 (37)	0.661	1.397	345	1.507	29x14	0.090	75	1.785	2472	14.3	2800
500 (37)	0.789	1.525	345	1.665	26x12	0.063	75	1.977	3240	15.8	4000
750 (61)	0.968	1.714	345	1.854	25x10	0.041	75	2.208	4480	17.7	6000
1000 (61)	1.117	1.863	345	2.003	32x10	0.032	75	2.357	5614	18.9	8000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Pulling tension based on pulling eye directly connected to conductor



**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (Solid)	0.128	0.162	0.065	0.057	0.142	8.7	0.216 + j0.752	0.162 + j0.055	2441	180	220
1 (19)	0.128	0.162	0.061	0.055	0.151	9.3	0.216 + j0.751	0.162 + j0.056	2441	180	220
1/0 (Solid)	0.102	0.128	0.061	0.055	0.152	9.3	0.182 + j0.749	0.128 + j0.053	3138	200	250
1/0 (19)	0.102	0.128	0.057	0.053	0.162	10.0	0.182 + j0.747	0.128 + j0.054	3138	200	250
2/0 (19)	0.081	0.102	0.053	0.051	0.174	10.7	0.156 + j0.743	0.102 + j0.052	3836	230	285
3/0 (19)	0.064	0.081	0.049	0.049	0.187	11.5	0.135 + j0.739	0.081 + j0.050	4882	260	320
4/0 (19)	0.051	0.065	0.046	0.048	0.202	12.4	0.119 + j0.735	0.065 + j0.048	6277	300	360
250 (37)	0.043	0.056	0.043	0.047	0.212	13.0	0.110 + j0.730	0.056 + j0.047	7323	325	
350 (37)	0.031	0.041	0.039	0.045	0.239	14.7	0.095 + j0.723	0.041 + j0.045	10113	390	460
500 (37)	0.022	0.030	0.034	0.043	0.271	16.6	0.084 + j0.714	0.030 + j0.043	14406	455	525
750 (61)	0.014	0.023	0.029	0.041	0.313	19.2	0.077 + j0.704	0.023 + j0.041	22019	545	580
1000 (61)	0.011	0.019	0.026	0.039	0.350	21.5	0.073 + j0.698	0.019 + j0.039	28184		

\*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

\*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

\*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.



**Table 3 – Weights and Measurements (Metric)**

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
1 (Solid)	7.34	25.83	8.76	28.63	7x14	1.23	1.27	34.42	1433	274.32	2977
1 (19)	8.18	26.67	8.76	29.46	7x14	1.23	1.27	35.26	1472	281.94	2977
1/0 (Solid)	8.23	26.72	8.76	29.51	9x14	0.96	1.27	35.31	1613	281.94	3756
1/0 (19)	9.17	27.66	8.76	30.45	9x14	0.96	1.27	36.25	1658	289.56	3756
2/0 (19)	10.29	28.78	8.76	31.57	11x14	0.78	1.27	37.36	1875	299.72	4735
3/0 (19)	11.58	30.07	8.76	32.87	14x14	0.61	1.27	38.66	2155	309.88	5972
4/0 (19)	13.00	31.50	8.76	34.29	18x14	0.48	1.27	40.08	2503	320.04	7529
250 (37)	14.17	32.87	8.76	35.66	21x14	0.41	1.91	42.72	2927	342.90	8900
350 (37)	16.79	35.48	8.76	38.28	29x14	0.30	1.91	45.34	3679	363.22	12460
500 (37)	20.04	38.73	8.76	42.29	26x12	0.21	1.91	50.22	4822	401.32	17800
750 (61)	24.59	43.54	8.76	47.09	25x10	0.13	1.91	56.08	6667	449.58	26700
1000 (61)	28.37	47.32	8.76	50.88	32x10	0.10	1.91	59.87	8355	480.06	35600

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Pulling tension based on pulling eye directly connected to conductor



**Table 4 – Electrical and Engineering Data (Metric)**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (Solid)	0.4199	0.53	0.0198	0.1870	0.466	28.5433	0.216 + j0.752	0.162 + j0.055	2441	180	220
1 (19)	0.4199	0.53	0.0186	0.1804	0.495	30.5118	0.216 + j0.751	0.162 + j0.056	2441	180	220
1/0 (Solid)	0.3346	0.42	0.0186	0.1804	0.499	30.5118	0.182 + j0.749	0.128 + j0.053	3138	200	250
1/0 (19)	0.3346	0.42	0.0174	0.1739	0.531	32.8084	0.182 + j0.747	0.128 + j0.054	3138	200	250
2/0 (19)	0.2657	0.33	0.0162	0.1673	0.571	35.1050	0.156 + j0.743	0.102 + j0.052	3836	230	285
3/0 (19)	0.2100	0.27	0.0149	0.1608	0.614	37.7297	0.135 + j0.739	0.081 + j0.050	4882	260	320
4/0 (19)	0.1673	0.21	0.0140	0.1575	0.663	40.6824	0.119 + j0.735	0.065 + j0.048	6277	300	360
250 (37)	0.1411	0.18	0.0131	0.1542	0.696	42.6509	0.110 + j0.730	0.056 + j0.047	7323	325	
350 (37)	0.1017	0.13	0.0119	0.1476	0.784	48.2283	0.095 + j0.723	0.041 + j0.045	10113	390	460
500 (37)	0.0722	0.10	0.0104	0.1411	0.889	54.4619	0.084 + j0.714	0.030 + j0.043	14406	455	525
750 (61)	0.0459	0.08	0.0088	0.1345	1.027	62.9921	0.077 + j0.704	0.023 + j0.041	22019	545	580
1000 (61)	0.0361	0.06	0.0079	0.1280	1.148	70.5381	0.073 + j0.698	0.019 + j0.039	28184		

\*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

\*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

\*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

CN  
Calculator



**Southwire**

**CABLETECH  
SUPPORT™**

Services