



## EPEC 40 (Schedule 40)



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

High-Density Polyethylene

### APPLICATIONS AND FEATURES:

Designed to house and protect wire and cable products in various underground applications for commercial constructions, EV infrastructure expansions, Utility grid-hardening efforts, airports, mass transit, renewables, petrochemical, agriculture, and data centers. May be installed directly buried or encased in concrete as permitted by The National Electrical Code® Article 353. For above ground applications, HDPE conduit must be encased in a minimum of 2 inches of concrete.

### SPECIFICATIONS:

- ASTM D3350 Standard Specification for Polyethylene Plastics Pipe and Fittings Materials
- ASTM F2160 Standard Specification for Solid Wall High Density Polyethylene (HDPE) Conduit Based on Controlled Outside Diameter (OD)
- UL 651A High Density Polyethylene (HPDE) Conduit
- CSA [CSA marking is available upon request](#)
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify “Made in the USA Only!” when ordering to ensure your project receives American made products.
- NEMA TC-7 Smooth-Wall Coilable Electrical Polyethylene Conduit

### SAMPLE PRINT LEGEND:

{SQFTG} FEET (LOGO) SOUTHWIRE CONDUIT (UL) HDPE X" SCH40 NEMA TC 7 / ASTM F2160 {MMM/DD/YYYY} {MACH/  
SHFT/OP}





**Table 1 – Physical and Electrical Data**

Stock Number	Duct Nominal Size	Duct Nominal Outside Dia.	Duct Min. Wall Thickness	Duct Nominal Inside Dia.	Duct Min. Bending Radius	Duct Max. Pull Tension	Duct Color	Approx. Cable and Duct Weight
	inch	inch	inch	inch	inch	lb		lb/1000ft
632260	0.75	1.050	0.113	0.804	12	710	GRY	149
TBA	1.00	1.315	0.133	1.029	14	1050	Optional	219
632028	1.25	1.660	0.140	1.360	18	1420	BK	297
632263	1.25	1.660	0.140	1.360	18	1420	GRY	297
633608	1.50	1.900	0.145	1.590	21	1700	ORG	354
632156	2.00	2.375	0.154	2.047	26	2280	BK	475
632266	2.00	2.375	0.154	2.047	26	2280	GRY	475
633607	2.00	2.375	0.154	2.047	26	2280	ORG	475
TBA	2.50	2.875	0.203	2.445	32	3615	Optional	749
TBA	3.00	3.500	0.216	3.042	39	4740	Optional	981
632385	4.00	4.500	0.237	3.998	50	6745	GRY	1396

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◇ Cable marked with this symbol is a standard stock item

**Cell Classification for HDPE Conduit**

Property	Test Method	Value
Density	D4883	0.953 g/cc
Melt Index	D1238	0.25 g/10 min
Flexural Modulus	D790	168,000 psi
Tensile Strength	D638	3900 yield @ 2 in/min
SP-NCLS ESCR	F2136	>1000 hrs
Hydrostatic Design Basis	D2837	N/A

- (PE436580C-BK), (PE436580E-Colors)

CIC Labor  
Saving  
Calculator

