



## Broadband Coax - RG6, RG59 and 18/2 Siamese




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

#### Non-Plenum Rated

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Polyethylene
3. **Shield:** Copper braid shielded
4. **Signal:** 2/C #18 Black, Red
5. **Jacket:** Polyvinyl Chloride PVC.

#### Plenum Rated

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Foamed Fluoropolymer
3. **Shield:** Copper braid shielded
4. **Signal:** 2/C #18 Black, Red
5. **Jacket:** Polyvinyl Chloride PVC.

### APPLICATIONS AND FEATURES:

CATV Applications for distributing television signals, using "F" connectors, ALUMINUM BRAID CCTV Applications for surveillance; Connecting security cameras, DVR or monitor using "BNC" connectors, COPPER BRAID

- Flame Test Non-Plenum: UL 1685/CSA FT1
- Flame Test Plenum: NFPA 262/CSA FT6

### SPECIFICATIONS:

- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test

### SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® SIGNAL® 993267 1C18 AWG RG 6/U 2C 18 AWG E57497 (UL) CM/CL2 SUN RES

{SQFTG} SOUTHWIRE® SIGNAL® 993265 1C18 AWG RG 6/U 2C 18 AWG TYPE CL2P/CMP C(ETL)US -- TYPE CMP FT6

{SQFTG} SOUTHWIRE® SIGNAL® 993254 1C20 AWG RG 59/U 2C18 AWG DIRECT BURIAL SUN RES



**Table 1 – Physical and Electrical Data**

Stock Number	Cable Type	Rating	Cond. Size	Cond. Number	Cond. Type	Cond. Strands	Insul. Thickness	Approx. OD	Approx. Weight	Shield Type	Application
			AWG	No.		strands	mil	inch	lb /1000ft		
RG6											
993267	RG6	CM	20	1	BC	Solid	70	0.126 x 0.455	59	Copper Braid	CATV
99326	RG6	CMP/ CL2P	22	1	CCS	Solid	60	0.228 x 0.396	46	Copper Braid	CATV
993265	RG6	CMP/ CL2P	18	1	BC	Solid	60	0.228 x 0.396	56	Copper Braid	CATV
RG59											
993253	RG59	CM	20	1	BC	Solid	55	0.166 x 0.124	50	Copper Braid	CATV
993256	RG59	CMP/ CL2P	20	1	BC	Solid	55	0.198 x 0.368	47	Copper Braid	CATV
993254	RG59	DIR BUR	20	1	BC	Solid	55	0.230 x 0.421	44	Copper Braid	CATV
99511	RG59	CM	20	1	BC	Solid	55	0.236 x 0.425	46	Copper Braid	CATV

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item