



## ROMEX® SIMpull® NMD90 Copper

300 Volts / -25°C Min, 90°C Max. Copper Conductors




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Solid per ASTM B3 or Combination unilay-stranded copper conductors per ASTM B787.
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath
3. **Jacket:** Polyvinyl Chloride PVC jacket utilizing SIMpull® Technology.

### APPLICATIONS AND FEATURES:

Southwire's Romex® SIMpull® NMD90 cables may be used for both exposed work in dry locations or concealed work in dry or damp locations.

The maximum allowable conductor temperature is 90°C. The minimum recommended installation temperature is -25°C for two-conductor cables and -10°C for three-conductor cables (with suitable handling procedures). Material should be properly stored above 0°C for 24 hours prior to installation. The maximum voltage rating for all intended applications is 300 volts. Consult the Canadian Electrical Code<sup>1</sup> for further information related to applications.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B787 19 Wire Combination Unilay-Stranded Copper Conductors
- CSA C22.2 No. 48 non-metallic sheathed cable
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202/FT4 Flame Test (70,000 BTU/hr) 350kcmil and Larger

### SAMPLE PRINT LEGEND:

SOUTHWIRE CSA LL90458 12 AWG 2 CDRS BLACK/WHITE NMD90 NYLON ROMEX(R) BRAND SIMpull (TM) (-25C) 300 VOLTS FT1 COVERED & MADE UNDER U.S. PAT. NOS 7557301 & 7411129. [Jacket Colour is yellow]





**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Conductor Number	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Jacket Thickness	Approx. OD	Copper Weight	Overall Weight
	AWG/ Kcmil		inch		mils	No. x AWG	mil	inch	lbs/1000ft	lbs/1000ft
<b>14 AWG   Solid</b>										
551373◇	14	2	0.064	Solid	35	1x14	30	0.196x0.396	37	69
672477◇	14	2	0.064	Solid	35	1x14	30	0.196x0.396	37	69
471748◇	14	2	0.064	Solid	35	1x14	30	0.196x0.396	37	69
471797◇	14	3	0.064	Solid	35	1x14	30	0.388	50	90
<b>12 AWG   Solid</b>										
472308◇	12	2	0.080	Solid	35	1x14	30	0.213x0.430	51	88
471755◇	12	2	0.080	Solid	35	1x14	30	0.213x0.430	51	88
471805◇	12	3	0.080	Solid	35	1x14	30	0.428	72	118
<b>10 AWG   Solid</b>										
471763◇	10	2	0.101	Solid	35	1x12	30	0.234x0.488	82	124
472316◇	10	2	0.101	Solid	35	1x12	30	0.234x0.488	82	124
471813◇	10	3	0.101	Solid	35	1x12	30	0.479	115	168
551038◇	8	2	0.141	7	40	1x10	45	0.316x0.694	133	210
471821◇	8	3	0.141	7	40	1x10	45	0.635	186	283
557881◇	6	2	0.177	7	50	1x8	45	0.374x0.800	213	339
471839◇	6	3	0.177	7	60	1x8	45	0.775	297	433
557727◇	4	2	0.225	7	50	1x8	60	0.839	311	463
557882◇	3	2	0.252	7	50	1x6	80	0.937	410	610
676254◇	3	3	0.252	7	50	1x6	80	1.029	574	822
557880◇	2	3	0.282	7	50	1x6	80	0.991	702	862

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◇ Cable marked with this symbol is a standard stock item





**Table 2 – Electrical and Engineering Data**

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
14 AWG   Solid							
14	2	1.6	2.631	3.170	0.058	20	25
14	2	1.6	2.631	3.170	0.058	20	25
14	2	1.6	2.631	3.170	0.058	20	25
14	3	1.5	2.631	3.170	0.058	20	25
12 AWG   Solid							
12	2	1.6	1.662	2.002	0.054	25	30
12	2	1.6	1.662	2.002	0.054	25	30
12	3	1.7	1.662	2.002	0.054	25	30
10 AWG   Solid							
10	2	2.0	1.040	1.253	0.050	35	40
10	2	2.0	1.040	1.253	0.050	35	40
10	3	1.9	1.040	1.253	0.050	35	40
8	2	2.8	0.653	0.786	0.052	50	55
8	3	2.5	0.653	0.786	0.052	50	55
6	2	3.2	0.411	0.495	0.051	65	75
6	3	3.1	0.411	0.495	0.051	65	75
4	2	3.3	0.258	0.310	0.048	85	95
3	2	3.7	0.205	0.246	0.047	100	115
3	3	5.1	0.205	0.246	0.047	100	115
2	3	3.9	0.162	0.195	0.045	115	130

† Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

† Ampacities have been adjusted for more than Three Current-Carrying Conductors.

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

