



## HVTECK CU 1/C 115TRXLPE TS PVC AIA PVC 8kV 100% CSA

Single Conductor, 115 Mils Tree Retardant Cross Linked Polyethylene, 100% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 115 Mils Tree Retardant Cross Linked Polyethylene 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Inner Jacket:** PVC inner jacket
7. **Armour:** Aluminum Interlocked Armour (AIA)
8. **Overall Jacket:** Orange Polyvinyl Chloride (PVC) Jacket

### APPLICATIONS AND FEATURES:

Southwire's 8kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)





- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

**SAMPLE PRINT LEGEND:**

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CU 115 TRXLPE AIA 8kV 100% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

**Table 1 – Weights and Measurements**

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight |
|------------|--------|-------------------------|--------------------------|------------------|---------------------------------|------------------------|------------------|--------------------------|------------|---------------|----------------|
| AWG/ Kcmil | No.    | inch                    | inch                     | mil              | inch                            | mil                    | inch             | mil                      | inch       | lb/1000ft     | lb/1000ft      |
| 2          | 7      | 0.282                   | 0.550                    | 115              | 0.610                           | 65                     | 0.982            | 50                       | 1.082      | 216           | 653            |
| 1          | 19     | 0.322                   | 0.590                    | 115              | 0.650                           | 65                     | 1.022            | 50                       | 1.122      | 271           | 734            |
| 1/0        | 19     | 0.361                   | 0.629                    | 115              | 0.689                           | 80                     | 1.091            | 50                       | 1.191      | 339           | 861            |
| 2/0        | 19     | 0.405                   | 0.673                    | 115              | 0.733                           | 80                     | 1.135            | 50                       | 1.235      | 425           | 976            |
| 3/0        | 19     | 0.456                   | 0.724                    | 115              | 0.784                           | 80                     | 1.186            | 50                       | 1.286      | 534           | 1120           |
| 4/0        | 19     | 0.512                   | 0.780                    | 115              | 0.840                           | 80                     | 1.352            | 50                       | 1.452      | 670           | 1306           |
| 250        | 37     | 0.558                   | 0.834                    | 115              | 0.894                           | 80                     | 1.406            | 50                       | 1.506      | 789           | 1465           |
| 350        | 37     | 0.661                   | 0.937                    | 115              | 0.997                           | 80                     | 1.509            | 60                       | 1.629      | 1101          | 1881           |
| 500        | 37     | 0.789                   | 1.065                    | 115              | 1.125                           | 80                     | 1.661            | 60                       | 1.781      | 1567          | 2471           |
| 750        | 61     | 0.968                   | 1.254                    | 115              | 1.314                           | 80                     | 1.850            | 60                       | 1.970      | 2342          | 3483           |
| 1000       | 61     | 1.117                   | 1.403                    | 115              | 1.463                           | 80                     | 1.999            | 60                       | 2.119      | 3117          | 4377           |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.





**Table 2 – Electrical and Engineering Data**

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|-------------------------|-----------------------------|--|--------------------------------|---|
| AWG/Kcmil  | inch               | lb               | Ω/1000ft             | Ω/1000ft             | MΩ*1000ft                   | Ω/1000ft                   | Ω/1000ft                | Ω/1000ft                    | Amp                                    | Amp                            | Amp                                     |
| 2          | 13.0               | 530              | 0.162                | 0.204                | 0.040                       | 0.053                      | 0.559 + j0.510          | 0.205 + j0.054              | 1920                                   | 215                            | 221                                     |
| 1          | 13.5               | 669              | 0.128                | 0.162                | 0.037                       | 0.050                      | 0.521 + j0.487          | 0.163 + j0.051              | 2044                                   | 245                            | 247                                     |
| 1/0        | 14.3               | 844              | 0.102                | 0.128                | 0.034                       | 0.049                      | 0.489 + j0.466          | 0.129 + j0.049              | 2165                                   | 278                            | 275                                     |
| 2/0        | 14.8               | 1064             | 0.081                | 0.102                | 0.031                       | 0.047                      | 0.465 + j0.445          | 0.103 + j0.048              | 2302                                   | 317                            | 306                                     |
| 3/0        | 15.4               | 1342             | 0.064                | 0.081                | 0.028                       | 0.046                      | 0.445 + j0.421          | 0.082 + j0.046              | 2459                                   | 357                            | 335                                     |
| 4/0        | 17.4               | 1692             | 0.051                | 0.065                | 0.026                       | 0.046                      | 0.427 + j0.397          | 0.066 + j0.046              | 2633                                   | 404                            | 369                                     |
| 250        | 18.1               | 2000             | 0.043                | 0.056                | 0.024                       | 0.045                      | 0.417 + j0.375          | 0.057 + j0.045              | 2800                                   | 456                            | 412                                     |
| 350        | 19.5               | 2800             | 0.031                | 0.041                | 0.021                       | 0.042                      | 0.397 + j0.337          | 0.042 + j0.042              | 3120                                   | 537                            | 456                                     |
| 500        | 21.4               | 4000             | 0.022                | 0.030                | 0.018                       | 0.040                      | 0.377 + j0.297          | 0.031 + j0.040              | 3516                                   | 616                            | 497                                     |
| 750        | 23.6               | 6000             | 0.014                | 0.023                | 0.015                       | 0.038                      | 0.354 + j0.249          | 0.024 + j0.038              | 4102                                   | 706                            | 551                                     |
| 1000       | 25.4               | 8000             | 0.011                | 0.019                | 0.013                       | 0.036                      | 0.336 + j0.218          | 0.020 + j0.036              | 4563                                   | 813                            | 596                                     |

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

\* CEC ampacities are based on:

3-1/C in air copper and aluminum: D17M

3-1/C direct buried copper and aluminum: D17A

**Table 3 – Weights and Measurements (Metric)**

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight |
|------------|--------|-------------------------|--------------------------|------------------|---------------------------------|------------------------|------------------|--------------------------|------------|---------------|----------------|
| AWG/Kcmil  | No.    | mm                      | mm                       | mm               | mm                              | mm                     | mm               | mm                       | mm         | kg/km         | kg/km          |
| 2          | 7      | 7.16                    | 13.97                    | 2.92             | 15.49                           | 1.65                   | 24.94            | 1.27                     | 27.48      | 321           | 972            |
| 1          | 19     | 8.18                    | 14.99                    | 2.92             | 16.51                           | 1.65                   | 25.96            | 1.27                     | 28.50      | 403           | 1092           |
| 1/0        | 19     | 9.17                    | 15.98                    | 2.92             | 17.50                           | 2.03                   | 27.71            | 1.27                     | 30.25      | 504           | 1281           |
| 2/0        | 19     | 10.29                   | 17.09                    | 2.92             | 18.62                           | 2.03                   | 28.83            | 1.27                     | 31.37      | 632           | 1452           |
| 3/0        | 19     | 11.58                   | 18.39                    | 2.92             | 19.91                           | 2.03                   | 30.12            | 1.27                     | 32.66      | 795           | 1667           |
| 4/0        | 19     | 13.00                   | 19.81                    | 2.92             | 21.34                           | 2.03                   | 34.34            | 1.27                     | 36.88      | 997           | 1944           |
| 250        | 37     | 14.17                   | 21.18                    | 2.92             | 22.71                           | 2.03                   | 35.71            | 1.27                     | 38.25      | 1174          | 2180           |
| 350        | 37     | 16.79                   | 23.80                    | 2.92             | 25.32                           | 2.03                   | 38.33            | 1.52                     | 41.38      | 1638          | 2799           |
| 500        | 37     | 20.04                   | 27.05                    | 2.92             | 28.58                           | 2.03                   | 42.19            | 1.52                     | 45.24      | 2332          | 3677           |
| 750        | 61     | 24.59                   | 31.85                    | 2.92             | 33.38                           | 2.03                   | 46.99            | 1.52                     | 50.04      | 3485          | 5183           |
| 1000       | 61     | 28.37                   | 35.64                    | 2.92             | 37.16                           | 2.03                   | 50.77            | 1.52                     | 53.82      | 4639          | 6514           |

All dimensions are nominal and subject to normal manufacturing tolerances





◇ Cable marked with this symbol is a standard stock item

1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 4 – Electrical and Engineering Data (Metric)**

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|-------------------------|-----------------------------|--|--------------------------------|---|
| AWG/Kcmil  | mm                 | newton           | Ω/km                 | Ω/km                 | MΩ*km                       | Ω/km                       | Ω/1000ft                | Ω/1000ft                    | Amp                                    | Amp                            | Amp                                     |
| 2          | 330.20             | 2359             | 0.5315               | 0.67                 | 0.0122                      | 0.1739                     | 0.559 + j0.510          | 0.205 + j0.054              | 1920                                   | 215                            | 221                                     |
| 1          | 342.90             | 2977             | 0.4199               | 0.53                 | 0.0113                      | 0.1640                     | 0.521 + j0.487          | 0.163 + j0.051              | 2044                                   | 245                            | 247                                     |
| 1/0        | 363.22             | 3756             | 0.3346               | 0.42                 | 0.0104                      | 0.1608                     | 0.489 + j0.466          | 0.129 + j0.049              | 2165                                   | 278                            | 275                                     |
| 2/0        | 375.92             | 4735             | 0.2657               | 0.33                 | 0.0094                      | 0.1542                     | 0.465 + j0.445          | 0.103 + j0.048              | 2302                                   | 317                            | 306                                     |
| 3/0        | 391.16             | 5972             | 0.2100               | 0.27                 | 0.0085                      | 0.1509                     | 0.445 + j0.421          | 0.082 + j0.046              | 2459                                   | 357                            | 335                                     |
| 4/0        | 441.96             | 7529             | 0.1673               | 0.21                 | 0.0079                      | 0.1509                     | 0.427 + j0.397          | 0.066 + j0.046              | 2633                                   | 404                            | 369                                     |
| 250        | 459.74             | 8900             | 0.1411               | 0.18                 | 0.0073                      | 0.1476                     | 0.417 + j0.375          | 0.057 + j0.045              | 2800                                   | 456                            | 412                                     |
| 350        | 495.30             | 12460            | 0.1017               | 0.13                 | 0.0064                      | 0.1378                     | 0.397 + j0.337          | 0.042 + j0.042              | 3120                                   | 537                            | 456                                     |
| 500        | 543.56             | 17800            | 0.0722               | 0.10                 | 0.0055                      | 0.1312                     | 0.377 + j0.297          | 0.031 + j0.040              | 3516                                   | 616                            | 497                                     |
| 750        | 599.44             | 26700            | 0.0459               | 0.08                 | 0.0046                      | 0.1247                     | 0.354 + j0.249          | 0.024 + j0.038              | 4102                                   | 706                            | 551                                     |
| 1000       | 645.16             | 35600            | 0.0361               | 0.06                 | 0.0040                      | 0.1181                     | 0.336 + j0.218          | 0.020 + j0.036              | 4563                                   | 813                            | 596                                     |

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

\* CEC ampacities are based on:

3-1/C in air copper and aluminum: D17M

3-1/C direct buried copper and aluminum: D17A

