



## TELCOFLEX® Small Cell Power Cable

600 Volt Tray Cable (TC-ER) Rated for Exposed Run. Flexible Tinned Copper Conductors. THHN, THWN Conductors rated 75°C Wet and 90°C Dry. Uninsulated, Flexible Tinned Copper Ground Wire and Drain Wire. Overall Aluminum Foil Shield and Tinned Copper Braid Shield. Overall TPE or PVC Jacket. Rated FT4 Flame Resistant, Sunlight Resistant and -40°C.




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class K Stranded Tinned Copper per ASTM B33, B172 & B174.
2. **Insulation:** Polyvinyl Chloride (PVC) Insulated Conductors with Nylon Sheath. Colors: Black, Red Color: 2 Conductor Construction - BLK, RED
3. **Ground:** Tinned Copper
4. **Drain Wire:** Tinned Copper  
Phase Size: 12awg. Drain Size/Strands: 16awg/7  
Phase Size: 10awg. Drain Size/Strands: 14awg/7  
Phase Size: 8 awg. Drain Size/Strands: 12awg/7
5. **Filler:** Polypropylene as needed to make round
6. **Tape Shield:** Aluminum/Poly/Aluminum (3-Layer) applied Helically over cabled assembly
7. **Braid Shield:** 34 AWG Tinned Copper with 85% coverage applied over Tape Shield
8. **Overall Jacket:** Black sunlight resistant thermoplastic Elastomer (TPE) Jacket

### APPLICATIONS AND FEATURES:

Southwire Tray Cable is suitable for use in industrial power or control circuits. Primary installations include cable trays, raceways and outdoor locations where supported by a messenger. These constructions are listed for exposed runs (TC-ER) per NEC 336.10. Listed for direct burial and for use in Class 1, Division 2 hazardous locations and Class 1 Control circuits. This cable may be used at temperatures not to exceed 75°C in wet locations and 90°C in dry locations.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- UL 2882 Outline of Investigation for Radio Head Cable
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy





**SAMPLE PRINT LEGEND:**

{SQFTG} SOUTHWIRE® E75755 {UL} X/C X AWG (XX.X{mm<sup>2</sup>}) XXX STRAND CLASS K + 1/C X AWG (X.XX{mm<sup>2</sup>}) GDING COND THHN/THWN 90°C DRY OR 75°C WET TYPE TC-ER 600V FT4 SUN RES

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Conductor	Insul. Thickness	Diameter Over Insulation	Jacket Thickness	Approx. OD	Approx. Weight
	AWG/ Kcmil	No.	No.	inch	mil	inch	mil	inch	lb/1000ft
TBA	14	2	41	0.077	20	0.117	45	0.353	85
TBA	12	2	65	0.101	20	0.141	45	0.41	146
673718	10	2	104	0.126	25	0.176	45	0.48	212
673717	8	2	168	0.157	35	0.227	60	0.6	282

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Max Pull Tension	Min Bending Radius	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	lb	inch	Amp	Amp
14	2.63	3.28		4	15	15
12	1.66	2.075		5	20	20
10	1.04	1.300		6	30	30
8	0.658	0.822		7	40	50

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

