



SFF-2 SEWF-2 150°C 600V

Silicone Rubber Glass Braid Fixture Wire - Flexible Stranded Conductors, Temp Rating 150°C




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Stranded tinned, annealed copper per ASTM B33
2. **Insulation:** Silicone Rubber
3. **Jacket:** Fiberglass braid jacket is applied over the insulation, then treated with a high temperature lacquer finish

APPLICATIONS AND FEATURES:

Used as motor lead wire or the wiring of electrical equipment and lighting fixtures, as well as hazardous location motors. Excellent electrical properties, flexible, good chemical resistance, contains no chlorine or other halogens, and fungus resistant. Colors available upon request.

SPECIFICATIONS:

- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL AWM Appliance wire approvals as listed in Table 1
- CSA Approved as shown in Table 1
- RoHS-3 Complies with European Directive 2015/863





Table 1 – Weights and Measurements

| Stock Number | Cond. Size | Cond. Strands | Insul. Thickness | Braid | Approx. OD | Approx. Weight | Temp. Rating | Standard (UL or other) |
|--------------|------------|---------------|------------------|-------|------------|----------------|--------------|------------------------|
| | AWG/Kcmil | strand | mil | mil | inch | lb/1000ft | °C | Style/Type |
| C0186B | 18 | 16 | 30 | 5 | 0.121 | 11 | 150 | 3070/SFF-2/SEWF-2 |
| C0166B | 16 | 26 | 30 | 5 | 0.132 | 16 | 150 | 3070/SFF-2/SEWF-2 |
| C0146B | 14 | 41 | 30 | 5 | 0.150 | 22 | 150 | 3070/SFF-2/SEWF-2 |
| C0126B | 12 | 65 | 30 | 5 | 0.170 | 31 | 150 | 3070 |
| C0106B | 10 | 105 | 45 | 5 | 0.227 | 52 | 150 | 3101 |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Dimensions and weights for other cable configurations are available upon request.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Weights and Measurements (Metric)

| Stock Number | Cond. Size | Cond. Strands | Insul. Thickness | Braid | Approx. OD | Approx. Weight | Temp. Rating | Standard (UL or other) |
|--------------|------------|---------------|------------------|-------|------------|----------------|--------------|------------------------|
| | AWG/Kcmil | strand | mm | mm | mm | kg/km | °C | Style/Type |
| C0186B | 18 | 16 | 0.76 | 0.13 | 3.07 | 16 | 150 | 3070/SFF-2/SEWF-2 |
| C0166B | 16 | 26 | 0.76 | 0.13 | 3.35 | 24 | 150 | 3070/SFF-2/SEWF-2 |
| C0146B | 14 | 41 | 0.76 | 0.13 | 3.81 | 33 | 150 | 3070/SFF-2/SEWF-2 |
| C0126B | 12 | 65 | 0.76 | 0.13 | 4.32 | 46 | 150 | 3070 |
| C0106B | 10 | 105 | 1.14 | 0.13 | 5.77 | 77 | 150 | 3101 |

