



Armorlite® Type MC THHN/THWN Circuit Size Copper Conductor Multi Circuits

Copper THHN/THWN Insulated Singles. Multiple Circuits Green Insulated Copper Grounding Conductor. UL Listed 600 Volts. Rated VW-1. Lightweight Aluminum Interlocked Armor.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid or 19 strands class C compressed copper per ASTM B3 and ASTM B8
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Ground:** Green insulated ground. Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
4. **Binder:** Mylar tape
5. **Armor:** Aluminum Interlocked Armor

Contact [Southwire SPEED™ Services](#) to request a quote.

APPLICATIONS AND FEATURES:

Southwire Armorlite® Type MC Cable - Multi-Circuit is suitable for use as follow:

- Multiple circuits for branch, feeder and service power distribution in commercial, industrial, institutional, and multi-residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2)
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Binder tape with print legend wrapped around assembly.
- Type THHN/THWN rated 90°C Dry.

Southwire Armorlite® Type MC Cable - Multi-Circuit meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire





- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

E96627 {UL} TYPE MC XX AWG THHN OR THWN CDRS WITH X X XX AWG NEUTRAL FOR USE IN CABLE TRAYS 600 VOLTS

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Num x Neutral Size	Diameter Over Armor	Copper Weight	Overall Weight
	AWG/ Kcmil		inch		mils	No. x AWG	No. x AWG	inch	lbs/1000ft	lbs/1000ft
12 AWG Solid										
555951◇	12	5	0.080	Solid	20	1x12	2x12	0.586	119	187
690057◇	12	6	0.080	Solid	20	1x12	2x12	0.586	139	211
563324◇	12	6	0.080	Solid	20	1x12	1x12	0.586	139	211
690065◇	12	8	0.080	Solid	20	1x12	2x12	0.661	179	266
596437◇	12	8	0.080	Solid	20	1x12	None	0.661	179	266
586407◇	12	9	0.080	Solid	20	1x12	4x12	0.709	199	294
690073◇	12	12	0.080	Solid	20	1x12	3x12	0.809	259	401
10 AWG Solid										
552970◇	10	6	0.101	Solid	25	1x10	2x10	0.679	216	311
587714◇	10	6	0.101	Solid	25	1x10	None	0.679	216	311
690081◇	10	8	0.101	Solid	25	1x10	2x10	0.759	278	417
552986◇	10	12	0.101	Solid	25	1x10	3x10	0.946	402	587

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

Note: Conductor number = Does not include green ground.





Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
12 AWG Solid							
12	5	4.1	1.662	2.002	0.054	20	24
12	6	4.1	1.662	2.002	0.054	20	24
12	6	4.1	1.662	2.002	0.054	20	24
12	8	4.6	1.662	2.002	0.054	17	21
12	8	4.6	1.662	2.002	0.054	17	21
12	9	5.0	1.662	2.002	0.054	17	21
12	12	5.7	1.662	2.002	0.054	12	15
10 AWG Solid							
10	6	4.8	1.040	1.253	0.050	28	32
10	6	4.8	1.040	1.253	0.050	28	32
10	8	5.3	1.040	1.253	0.050	24	28
10	12	6.6	1.040	1.253	0.050	17	20

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

Color Table

Stock Number	Cond. Size	Cond. Num.	1	2	3	4	5	6	7	8	9	10	11	12	13
555951	12	5	Black	Red	Blue	White	Green								
690057	12	6	Black	Red	Blue	White	Green								
563324	12	6	Black	Red	Blue	White	Green								
690065	12	8	Black	Red	Blue	White	Green								
596437	12	8	Black	Red	Blue	White	Green								
586407	12	9	Black	Red	Blue	White	Green								
690073	12	12	Black	Red	Blue	White	Green								
552970	10	6	Black	Red	Blue	White	Green								
587714	10	6	Black	Red	Blue	White	Green								
690081	10	8	Black	Red	Blue	White	Green								
552986	10	12	Black	Red	Blue	White	Green								

