



15kV AL 100% EPR (EAM) One-Third Neutral LLDPE

Single Conductor, 175 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM), 100% Insulation Level, One-third Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Moisture blocked class B compressed Aluminum ASTM B231 1350 ¾ hard H16/H26 (Non Moisture Blocked Optional)
- Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
- Insulation:** 175 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM) 100% insulation level
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Concentric Neutral:** Helically applied soft drawn bare copper one-third concentric neutral
- Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 15kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation. 140°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B609 Standard Specification for Aluminum 1350 Round Wire, Annealed and Intermediate Tempers, for Electrical Purposes
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] AL 15000 VOLTS EPR INSULATION 175 MILS -- (NESC) --
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET





Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
TBA	2 (Solid)	0.257	0.645	175	0.735	3x14	0.876	50	0.963	385	7.7	398
629459	2 (7)	0.282	0.663	175	0.753	6x14	0.438	50	0.981	461	7.8	398
TBA	1 (Solid)	0.289	0.677	175	0.767	4x14	0.657	50	0.995	429	8.0	502
TBA	1 (19)	0.322	0.710	175	0.800	4x14	0.657	50	1.028	445	8.2	502
TBA	1/0 (Solid)	0.324	0.712	175	0.802	5x14	0.526	50	1.030	481	8.2	633
TBA	1/0 (19)	0.351	0.739	175	0.829	5x14	0.526	50	1.057	494	8.5	633
TBA	2/0 (19)	0.395	0.783	175	0.873	7x14	0.375	50	1.101	567	8.8	798
TBA	3/0 (19)	0.443	0.831	175	0.921	8x14	0.328	50	1.149	636	9.2	1006
629466	4/0 (19)	0.498	0.878	175	0.968	11x14	0.239	50	1.196	779	9.6	1269
TBA	250 (37)	0.558	0.954	175	1.044	12x14	0.219	50	1.272	828	10.2	1500
TBA	350 (37)	0.661	1.057	175	1.167	17x14	0.154	50	1.395	1059	11.2	2100
622454	500 (37)	0.789	1.185	175	1.295	25x14	0.105	50	1.523	1371	12.2	3000
622583?	750 (61)	0.968	1.368	175	1.478	24x12	0.069	75	1.793	2051	14.3	4500
621828	1000 (61)	1.117	1.517	175	1.627	20x10	0.052	75	1.984	2597	15.9	6000

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

† Solid Black Jacket





Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2 (Solid)	0.162	0.204	0.040	0.052	0.212	15.8	0.256 + j0.754	0.204 + j0.053	1144	120	150
2 (7)	0.266	0.336	0.037	0.050	0.228	17.0	0.389 + j0.763	0.336 + j0.051	2092	120	150
1 (Solid)	0.129	0.162	0.037	0.050	0.228	17.0	0.215 + j0.756	0.162 + j0.051	1443	140	175
1 (19)	0.211	0.266	0.035	0.048	0.244	18.2	0.319 + j0.752	0.266 + j0.049	1443	140	175
1/0 (Solid)	0.102	0.128	0.035	0.048	0.246	18.3	0.181 + j0.756	0.128 + j0.049	1821	155	195
1/0 (19)	0.167	0.211	0.033	0.047	0.259	19.3	0.264 + j0.753	0.211 + j0.048	1821	155	195
2/0 (19)	0.133	0.167	0.030	0.045	0.280	20.9	0.221 + j0.752	0.167 + j0.046	2296	180	220
3/0 (19)	0.105	0.132	0.028	0.044	0.303	22.6	0.186 + j0.749	0.132 + j0.044	2895	200	250
4/0 (19)	0.084	0.105	0.025	0.042	0.336	25.0	0.159 + j0.746	0.105 + j0.043	3836	235	285
250 (37)	0.071	0.090	0.023	0.041	0.363	27.0	0.144 + j0.741	0.090 + j0.041	4313	256	309
350 (37)	0.050	0.065	0.020	0.039	0.412	30.7	0.119 + j0.734	0.065 + j0.039	6038	310	370
500 (37)	0.035	0.046	0.018	0.037	0.474	35.3	0.100 + j0.726	0.046 + j0.037	8626	370	445
750 (61)	0.024	0.033	0.015	0.036	0.573	42.7	0.087 + j0.714	0.033 + j0.036	13298	460	525
1000 (61)	0.018	0.026	0.013	0.035	0.645	48.0	0.080 + j0.705	0.026 + j0.036	17615	520	575

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.





Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/ Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
TBA	2 (Solid)	6.53	16.38	4.44	18.67	3x14	2.87	1.27	24.46	573	195.58	1771
629459	2 (7)	7.16	16.84	4.44	19.13	6x14	1.44	1.27	24.92	686	198.12	1771
TBA	1 (Solid)	7.34	17.20	4.44	19.48	4x14	2.16	1.27	25.27	638	203.20	2234
TBA	1 (19)	8.18	18.03	4.44	20.32	4x14	2.16	1.27	26.11	662	208.28	2234
TBA	1/0 (Solid)	8.23	18.08	4.44	20.37	5x14	1.73	1.27	26.16	716	208.28	2817
TBA	1/0 (19)	8.92	18.77	4.44	21.06	5x14	1.73	1.27	26.85	735	215.90	2817
TBA	2/0 (19)	10.03	19.89	4.44	22.17	7x14	1.23	1.27	27.97	844	223.52	3551
TBA	3/0 (19)	11.25	21.11	4.44	23.39	8x14	1.08	1.27	29.18	946	233.68	4477
629466	4/0 (19)	12.65	22.30	4.44	24.59	11x14	0.78	1.27	30.38	1159	243.84	5647
TBA	250 (37)	14.17	24.23	4.44	26.52	12x14	0.72	1.27	32.31	1232	259.08	6675
TBA	350 (37)	16.79	26.85	4.44	29.64	17x14	0.51	1.27	35.43	1576	284.48	9345
622454	500 (37)	20.04	30.10	4.44	32.89	25x14	0.34	1.27	38.68	2040	309.88	13350
622583?	750 (61)	24.59	34.75	4.44	37.54	24x12	0.23	1.91	45.54	3052	363.22	20025
621828	1000 (61)	28.37	38.53	4.44	41.33	20x10	0.17	1.91	50.39	3865	403.86	26700

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

† Solid Black Jacket





Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2 (Solid)	0.5315	0.67	0.0122	0.1706	0.696	51.8373	0.256 + j0.754	0.204 + j0.053	1144	120	150
2 (7)	0.8727	1.10	0.0113	0.1640	0.748	55.7743	0.389 + j0.763	0.336 + j0.051	2092	120	150
1 (Solid)	0.4232	0.53	0.0113	0.1640	0.748	55.7743	0.215 + j0.756	0.162 + j0.051	1443	140	175
1 (19)	0.6923	0.87	0.0107	0.1575	0.801	59.7113	0.319 + j0.752	0.266 + j0.049	1443	140	175
1/0 (Solid)	0.3346	0.42	0.0107	0.1575	0.807	60.0394	0.181 + j0.756	0.128 + j0.049	1821	155	195
1/0 (19)	0.5479	0.69	0.0101	0.1542	0.850	63.3202	0.264 + j0.753	0.211 + j0.048	1821	155	195
2/0 (19)	0.4364	0.55	0.0091	0.1476	0.919	68.5696	0.221 + j0.752	0.167 + j0.046	2296	180	220
3/0 (19)	0.3445	0.43	0.0085	0.1444	0.994	74.1470	0.186 + j0.749	0.132 + j0.044	2895	200	250
4/0 (19)	0.2756	0.34	0.0076	0.1378	1.102	82.0210	0.159 + j0.746	0.105 + j0.043	3836	235	285
250 (37)	0.2329	0.30	0.0070	0.1345	1.191	88.5827	0.144 + j0.741	0.090 + j0.041	4313	256	309
350 (37)	0.1640	0.21	0.0061	0.1280	1.352	100.7218	0.119 + j0.734	0.065 + j0.039	6038	310	370
500 (37)	0.1148	0.15	0.0055	0.1214	1.555	115.8136	0.100 + j0.726	0.046 + j0.037	8626	370	445
750 (61)	0.0787	0.11	0.0046	0.1181	1.880	140.0919	0.087 + j0.714	0.033 + j0.036	13298	460	525
1000 (61)	0.0591	0.09	0.0040	0.1148	2.116	157.4803	0.080 + j0.705	0.026 + j0.036	17615	520	575

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

CN
Calculator

