



## 15kV CU 100% EPR (EAM) One-Third Neutral LLDPE

Single Conductor, 175 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM), 100% Insulation Level, One-third Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8; (Conductor moisture block optional and tinned copper per ASTM B33 optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer. A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 175 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM) 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Neutral:** Helically applied soft drawn bare copper one-third concentric neutral
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, Black (red extruded stripes optional); PowerGlide® LLDPE jacket optional

### APPLICATIONS AND FEATURES:

Southwire's 15kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

### SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 15000 VOLTS EPR INSULATION 175 MILS -- (NESC) --  
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET



**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
TBA	2 (Solid)	0.257	0.645	175	0.735	5x14	0.526	50	0.963	555	7.7	530
628070	2 (7)	0.282	0.663	175	0.753	6x14	0.438	50	0.981	604	7.8	530
TBA	2 (7)	0.282	0.670	175	0.760	5x14	0.526	50	0.988	567	7.9	530
TBA	1 (Solid)	0.289	0.677	175	0.767	7x14	0.375	50	0.995	651	8.0	669
TBA	1 (19)	0.322	0.710	175	0.800	7x14	0.375	50	1.028	668	8.2	669
TBA	1/0 (Solid)	0.324	0.712	175	0.802	9x14	0.292	50	1.030	763	8.2	844
628074	1/0 (19)	0.361	0.742	175	0.832	9x14	0.292	50	1.060	805	8.5	844
TBA	1/0 (19)	0.361	0.749	175	0.839	9x14	0.292	50	1.067	781	8.5	844
628077	2/0 (19)	0.405	0.786	175	0.876	11x14	0.239	50	1.104	939	8.8	1064
TBA	2/0 (19)	0.405	0.793	175	0.883	11x14	0.239	50	1.111	914	8.9	1064
TBA	3/0 (19)	0.456	0.844	175	0.934	14x14	0.187	50	1.162	1087	9.3	1342
623352	4/0 (19)	0.512	0.892	175	0.982	18x14	0.146	50	1.210	1327	9.7	1692
TBA	4/0 (19)	0.512	0.900	175	0.990	17x14	0.154	50	1.218	1291	9.7	1692
TBA	250 (37)	0.558	0.954	175	1.044	20x14	0.131	50	1.272	1478	10.2	2000
628080	350 (37)	0.661	1.051	175	1.161	18x12	0.092	50	1.422	2032	11.4	2800
619989	500 (37)	0.789	1.179	175	1.289	26x12	0.063	50	1.550	2720	12.4	4000
621464^	500 (37)	0.789	1.179	175	1.289	17x10	0.061	50	1.592	2782	12.7	4000
628083	500 (37)	0.789	1.179	175	1.289	17x10	0.061	50	1.592	2782	12.7	4000
628084	750 (61)	0.968	1.368	175	1.478	25x10	0.041	75	1.835	4009	14.7	6000
623507	1000 (61)	1.117	1.517	175	1.627	26x9	0.031	75	2.009	5148	16.1	8000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Pulling tension based on pulling eye directly connected to conductor

^ Solid Black Jacket



**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2 (Solid)	0.162	0.204	0.040	0.052	0.212	15.8	0.257 + j0.764	0.204 + j0.053	1876	160	195
2 (7)	0.162	0.204	0.037	0.050	0.228	17.0	0.257 + j0.763	0.204 + j0.051	2092	160	195
2 (7)	0.162	0.204	0.038	0.050	0.225	16.8	0.257 + j0.761	0.204 + j0.051	1876	160	195
1 (Solid)	0.128	0.162	0.037	0.050	0.228	17.0	0.216 + j0.764	0.162 + j0.051	2367	180	220
1 (19)	0.128	0.162	0.035	0.048	0.244	18.2	0.216 + j0.760	0.162 + j0.049	2367	180	220
1/0 (Solid)	0.102	0.128	0.035	0.048	0.246	18.3	0.182 + j0.762	0.128 + j0.049	2986	200	250
1/0 (19)	0.102	0.128	0.032	0.046	0.268	20.0	0.182 + j0.758	0.128 + j0.047	3138	200	250
1/0 (19)	0.102	0.128	0.032	0.047	0.264	19.7	0.182 + j0.758	0.128 + j0.047	2986	200	250
2/0 (19)	0.081	0.102	0.029	0.045	0.289	21.5	0.156 + j0.754	0.102 + j0.045	3836	230	285
2/0 (19)	0.081	0.102	0.030	0.045	0.285	21.2	0.156 + j0.754	0.102 + j0.045	3764	230	285
3/0 (19)	0.064	0.081	0.027	0.043	0.309	23.0	0.135 + j0.750	0.081 + j0.044	4746	260	320
4/0 (19)	0.051	0.065	0.025	0.041	0.343	25.5	0.119 + j0.746	0.065 + j0.042	6277	300	360
4/0 (19)	0.051	0.065	0.025	0.042	0.337	25.1	0.119 + j0.746	0.065 + j0.042	5984	300	360
250 (37)	0.043	0.056	0.023	0.041	0.363	27.0	0.110 + j0.742	0.056 + j0.041	7071	325	
350 (37)	0.031	0.041	0.020	0.039	0.418	31.1	0.095 + j0.733	0.041 + j0.040	9973	390	460
500 (37)	0.022	0.030	0.017	0.037	0.481	35.8	0.084 + j0.725	0.030 + j0.038	14406	455	525
500 (37)	0.022	0.030	0.017	0.038	0.481	35.8	0.084 + j0.723	0.030 + j0.039	14973	455	525
500 (37)	0.022	0.030	0.017	0.038	0.481	35.8	0.084 + j0.723	0.030 + j0.039	14973	455	525
750 (61)	0.014	0.023	0.015	0.036	0.573	42.7	0.077 + j0.713	0.023 + j0.037	22019	545	580
1000 (61)	0.011	0.019	0.013	0.035	0.645	48.0	0.073 + j0.705	0.019 + j0.036	28878		

\*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

\*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

\*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.



**Table 3 – Weights and Measurements (Metric)**

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/ Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
TBA	2 (Solid)	6.53	16.38	4.44	18.67	5x14	1.73	1.27	24.46	826	195.58	2359
628070	2 (7)	7.16	16.84	4.44	19.13	6x14	1.44	1.27	24.92	899	198.12	2359
TBA	2 (7)	7.16	17.02	4.44	19.30	5x14	1.73	1.27	25.10	844	200.66	2359
TBA	1 (Solid)	7.34	17.20	4.44	19.48	7x14	1.23	1.27	25.27	969	203.20	2977
TBA	1 (19)	8.18	18.03	4.44	20.32	7x14	1.23	1.27	26.11	994	208.28	2977
TBA	1/0 (Solid)	8.23	18.08	4.44	20.37	9x14	0.96	1.27	26.16	1135	208.28	3756
628074	1/0 (19)	9.17	18.85	4.44	21.13	9x14	0.96	1.27	26.92	1198	215.90	3756
TBA	1/0 (19)	9.17	19.02	4.44	21.31	9x14	0.96	1.27	27.10	1162	215.90	3756
628077	2/0 (19)	10.29	19.96	4.44	22.25	11x14	0.78	1.27	28.04	1397	223.52	4735
TBA	2/0 (19)	10.29	20.14	4.44	22.43	11x14	0.78	1.27	28.22	1360	226.06	4735
TBA	3/0 (19)	11.58	21.44	4.44	23.72	14x14	0.61	1.27	29.51	1618	236.22	5972
623352	4/0 (19)	13.00	22.66	4.44	24.94	18x14	0.48	1.27	30.73	1975	246.38	7529
TBA	4/0 (19)	13.00	22.86	4.44	25.15	17x14	0.51	1.27	30.94	1921	246.38	7529
TBA	250 (37)	14.17	24.23	4.44	26.52	20x14	0.43	1.27	32.31	2200	259.08	8900
628080	350 (37)	16.79	26.70	4.44	29.49	18x12	0.30	1.27	36.12	3024	289.56	12460
619989	500 (37)	20.04	29.95	4.44	32.74	26x12	0.21	1.27	39.37	4048	314.96	17800
621464^	500 (37)	20.04	29.95	4.44	32.74	17x10	0.20	1.27	40.44	4140	322.58	17800
628083	500 (37)	20.04	29.95	4.44	32.74	17x10	0.20	1.27	40.44	4140	322.58	17800
628084	750 (61)	24.59	34.75	4.44	37.54	25x10	0.13	1.91	46.61	5966	373.38	26700
623507	1000 (61)	28.37	38.53	4.44	41.33	26x9	0.10	1.91	51.03	7661	408.94	35600

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Pulling tension based on pulling eye directly connected to conductor

^ Solid Black Jacket



**Table 4 – Electrical and Engineering Data (Metric)**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2 (Solid)	0.5315	0.67	0.0122	0.1706	0.696	51.8373	0.257 + j0.764	0.204 + j0.053	1876	160	195
2 (7)	0.5315	0.67	0.0113	0.1640	0.748	55.7743	0.257 + j0.763	0.204 + j0.051	2092	160	195
2 (7)	0.5315	0.67	0.0116	0.1640	0.738	55.1181	0.257 + j0.761	0.204 + j0.051	1876	160	195
1 (Solid)	0.4199	0.53	0.0113	0.1640	0.748	55.7743	0.216 + j0.764	0.162 + j0.051	2367	180	220
1 (19)	0.4199	0.53	0.0107	0.1575	0.801	59.7113	0.216 + j0.760	0.162 + j0.049	2367	180	220
1/0 (Solid)	0.3346	0.42	0.0107	0.1575	0.807	60.0394	0.182 + j0.762	0.128 + j0.049	2986	200	250
1/0 (19)	0.3346	0.42	0.0098	0.1509	0.879	65.6168	0.182 + j0.758	0.128 + j0.047	3138	200	250
1/0 (19)	0.3346	0.42	0.0098	0.1542	0.866	64.6325	0.182 + j0.758	0.128 + j0.047	2986	200	250
2/0 (19)	0.2657	0.33	0.0088	0.1476	0.948	70.5381	0.156 + j0.754	0.102 + j0.045	3836	230	285
2/0 (19)	0.2657	0.33	0.0091	0.1476	0.935	69.5538	0.156 + j0.754	0.102 + j0.045	3764	230	285
3/0 (19)	0.2100	0.27	0.0082	0.1411	1.014	75.4593	0.135 + j0.750	0.081 + j0.044	4746	260	320
4/0 (19)	0.1673	0.21	0.0076	0.1345	1.125	83.6614	0.119 + j0.746	0.065 + j0.042	6277	300	360
4/0 (19)	0.1673	0.21	0.0076	0.1378	1.106	82.3491	0.119 + j0.746	0.065 + j0.042	5984	300	360
250 (37)	0.1411	0.18	0.0070	0.1345	1.191	88.5827	0.110 + j0.742	0.056 + j0.041	7071	325	
350 (37)	0.1017	0.13	0.0061	0.1280	1.371	102.0341	0.095 + j0.733	0.041 + j0.040	9973	390	460
500 (37)	0.0722	0.10	0.0052	0.1214	1.578	117.4541	0.084 + j0.725	0.030 + j0.038	14406	455	525
500 (37)	0.0722	0.10	0.0052	0.1247	1.578	117.4541	0.084 + j0.723	0.030 + j0.039	14973	455	525
500 (37)	0.0722	0.10	0.0052	0.1247	1.578	117.4541	0.084 + j0.723	0.030 + j0.039	14973	455	525
750 (61)	0.0459	0.08	0.0046	0.1181	1.880	140.0919	0.077 + j0.713	0.023 + j0.037	22019	545	580
1000 (61)	0.0361	0.06	0.0040	0.1148	2.116	157.4803	0.073 + j0.705	0.019 + j0.036	28878		CN

\*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3  
 \*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.  
 \*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

Calculator

