



CU Compressed 8kV NLEPR Insulation 133% IL LSZH-TP Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Single Conductor Copper, 140 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP) Jacket, Dual Rated UL/CSA. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 140 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP)

APPLICATIONS AND FEATURES:

Southwire's 8KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -25°C for cold bend. ST1 (low smoke) Rated for sizes 1/0 and larger. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4-ST1 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)





- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE/HWC-LIFEGUARD {UL} XXX KCMIL CU 140 MILS EPR SOLONON® 8KV 133% INS LEVEL MV-105 25%TS LS FOR CT USE SUN. RES. {NESC}

Table 1 – Weights and Measurements

Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size
AWG/Kcmil	No. of Strands	inch	inch	inch	mil	inch	lb/1000ft	lb/1000ft	lb	inch	inch
2	7	0.282	0.600	0.660	55	0.790	217	439	530	9.4	2.5
1	19	0.322	0.640	0.700	80	0.880	272	554	669	10.5	2.5
1/0	19	0.361	0.679	0.739	80	0.919	339	639	844	11.0	3.0
2/0	19	0.405	0.724	0.784	80	0.964	475	795	1064	11.5	3.0
3/0	19	0.456	0.774	0.834	80	1.014	534	878	1342	12.1	3.0
4/0	19	0.512	0.816	0.876	80	1.056	726	1090	1692	12.6	3.0
250	37	0.558	0.884	0.944	80	1.124	789	1189	2000	13.4	3.5
350	37	0.661	0.987	1.047	80	1.227	1101	1550	2800	14.7	3.5
500	37	0.789	1.092	1.152	80	1.332	1636	2133	4000	15.9	4.0
750	61	0.968	1.304	1.364	80	1.544	2343	2947	6000	18.5	4.5
1000	61	1.117	1.453	1.513	110	1.753	3118	3896	8000	21.0	5.0

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Conduit size based on 3 phase 40% fill-factor without ground

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.204	0.039	0.045	0.450 + j0.392	0.081 + j0.041	2075	155/165	195/215
1	0.128	0.162	0.035	0.045	0.451 + j0.468	0.081 + j0.035	2199	175/185	225/250
1/0	0.102	0.128	0.032	0.043	0.451 + j0.468	0.081 + j0.035	2320	200/215	260/290
2/0	0.081	0.102	0.030	0.042	0.451 + j0.468	0.081 + j0.035	2456	230/245	300/335
3/0	0.064	0.081	0.027	0.040	0.451 + j0.468	0.081 + j0.035	2614	260/275	345/385
4/0	0.051	0.065	0.025	0.039	0.451 + j0.468	0.081 + j0.035	2788	295/315	400/445
250	0.043	0.056	0.024	0.038	0.451 + j0.468	0.081 + j0.035	2955	325/345	445/495
350	0.031	0.041	0.020	0.036	0.451 + j0.468	0.081 + j0.035	3274	390/415	550/610
500	0.022	0.030	0.018	0.034	0.451 + j0.468	0.081 + j0.035	3671	465/500	685/765
750	0.014	0.023	0.015	0.032	0.452 + j0.366	0.091 + j0.043	4257	565/610	885/990
1000	0.011	0.019	0.013	0.032	0.452 + j0.422	0.081 + j0.039	4718	640/690	1060/1185





- * NEC ampacities are based on:
 - * For Duct: Table 310.60(C)(11) Detail 1.
 - * For Free Air: Table 310.60(C)(3).
- * Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
- * Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.
- * Capacitive Reactance is between Phase-to-Shield.

