

# 35kV AL 100% TRXLPE One-Half (Based on Short Circuit) HI-DRI-PLUS®. Renewable (Solar or Wind)

Moisture Blocked Aluminum Conductors. TRXLP Insulation. One-Half Copper Concentric Neutrals. XLPE Jacket




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Moisture Blocked 1350 H16/H26 Aluminum, Class B Compressed or Compressed Unilay Stranded
- Strand Shield:** Semi-conducting Crosslinked Polyethylene
- Insulation:** Tree Retardant Crosslinked Polyethylene (TRXLP)
- Insulation Shield:** Strippable Semi-conducting Crosslinked Polyethylene
- Concentric Neutral:** Annealed Copper Wires Helically Applied One-Half Concentric Neutral
- Overall Jacket & Water Block:** HI-DRI-PLUS® Water Swellable Powder Black Crosslinked Polyethylene (XLPE) with Red Extruded Stripes

## APPLICATIONS AND FEATURES:

- Predominately used for renewable projects with wind or solar applications.
- Suitable for use in wet or dry locations, direct burial, underground ducts, and exposure to direct sunlight.
- To be used at conductor temperature not to exceed 105°C normal operation.
- UL listed MV-105
- The concentric neutral count and size listed in Table 1 are based on the ICEA P-45-482 short circuit calculation of an MV-90 design. The short circuit value in Table 1 is calculated using a higher thermal limit of a crosslinked XLPE jacket MV-105 design.

## SPECIFICATIONS:

- UL 1072 Medium-Voltage Power Cables
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

## SAMPLE PRINT LEGEND:

SOUTHWIRE(R) HI-DRI(R) (UL) XXX AWG AL 345 MILS TRXLPE TYPE MV-105 35KV 100% INSUL LEVEL -- (NESC) --  
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)



Southwire

**CABLETECH  
SUPPORT™**

Services

**Table 1 – Weights and Measurements**

| Stock Number | Cond. Size | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Concentric Neutral | Neutral DC Resistance 25°C | Jacket Thickness | Approx. OD | Approx. Weight | Min Bending Radius | Max Pull Tension |
|--------------|------------|-------------------------|--------------------------|------------------|---------------------------------|--------------------|----------------------------|------------------|------------|----------------|--------------------|------------------|
|              | AWG/Kcmil  | inch                    | inch                     | mil              | inch                            | No. x AWG          | Ω /1000ft                  | mil              | inch       | lb / 1000ft    | inch               | lb               |
| 662906       | 1/0 (19)   | 0.361                   | 1.072                    | 345              | 1.182                           | 6x14               | 0.438                      | 50               | 1.410      | 783            | 11.3               | 633              |
| TBA          | 2/0 (19)   | 0.395                   | 1.123                    | 345              | 1.233                           | 7x14               | 0.375                      | 50               | 1.461      | 912            | 11.7               | 798              |
| 626306       | 4/0 (19)   | 0.498                   | 1.218                    | 345              | 1.328                           | 12x14              | 0.219                      | 50               | 1.556      | 1062           | 12.4               | 1269             |
| TBA          | 250 (37)   | 0.558                   | 1.294                    | 345              | 1.404                           | 14x14              | 0.187                      | 75               | 1.682      | 1332           | 13.5               | 1500             |
| TBA          | 350 (37)   | 0.661                   | 1.397                    | 345              | 1.507                           | 19x14              | 0.138                      | 75               | 1.785      | 1579           | 14.3               | 2100             |
| TBA          | 500 (37)   | 0.789                   | 1.525                    | 345              | 1.665                           | 27x14              | 0.097                      | 75               | 1.943      | 1976           | 15.5               | 3000             |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**Table 2 – Electrical and Engineering Data**

| Cond. Size | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Charging Current | Dielectric Loss | Zero Sequence Impedance | Positive Sequence Impedance | Short Circuit Current @ 30 Cycle | Allowable Ampacity in Duct 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|----------------------|----------------------|-----------------------------|----------------------------|------------------|-----------------|-------------------------|-----------------------------|----------------------------------|---------------------------------|---|
| AWG/Kcmil  | Ω/1000ft             | Ω/1000ft             | MΩ*1000ft                   | Ω/1000ft                   | A/1000ft         | W/1000ft        | Ω/1000ft                | Ω/1000ft                    | Amp                              | Amp                             | Amp                                     |
| 1/0 (19)   | 0.167                | 0.211                | 0.071                       | 0.053                      | 0.28             | 1.71            | 0.265 + j0.747          | 0.211 + j0.054              | 3103                             | 160                             | 195                                     |
| 2/0 (19)   | 0.133                | 0.167                | 0.067                       | 0.052                      | 0.30             | 1.80            | 0.221 + j0.744          | 0.167 + j0.051              | 3621                             | 185                             | 220                                     |
| 4/0 (19)   | 0.084                | 0.105                | 0.058                       | 0.048                      | 0.34             | 2.08            | 0.159 + j0.735          | 0.105 + j0.048              | 6207                             | 235                             | 280                                     |
| 250 (37)   | 0.071                | 0.090                | 0.054                       | 0.047                      | 0.37             | 2.24            | 0.144 + j0.730          | 0.090 + j0.047              | 7242                             |                                 |   |
| 350 (37)   | 0.050                | 0.065                | 0.048                       | 0.045                      | 0.42             | 2.52            | 0.119 + j0.723          | 0.065 + j0.045              | 9828                             | 315                             | 370                                     |
| 500 (37)   | 0.035                | 0.046                | 0.042                       | 0.042                      | 0.47             | 2.86            | 0.100 + j0.715          | 0.046 + j0.043              | 13967                            | 380                             | 435                                     |

\*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

\*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

\*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.



**Table 3 – Weights and Measurements (Metric)**

| Stock Number | Cond. Size | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Concentric Neutral | Neutral DC Resistance 25°C | Jacket Thickness | Approx. OD | Approx. Weight | Min Bending Radius | Max Pull Tension |
|--------------|------------|-------------------------|--------------------------|------------------|---------------------------------|--------------------|----------------------------|------------------|------------|----------------|--------------------|------------------|
|              | AWG/Kcmil  | mm                      | mm                       | mm               | mm                              | No. x AWG          | Ω/km                       | mm               | mm         | kg/km          | mm                 | newton           |
| 662906       | 1/0 (19)   | 9.17                    | 27.23                    | 8.76             | 30.02                           | 6x14               | 1.44                       | 1.27             | 35.81      | 1165           | 287.02             | 2817             |
| TBA          | 2/0 (19)   | 10.03                   | 28.52                    | 8.76             | 31.32                           | 7x14               | 1.23                       | 1.27             | 37.11      | 1357           | 297.18             | 3551             |
| 626306       | 4/0 (19)   | 12.65                   | 30.94                    | 8.76             | 33.73                           | 12x14              | 0.72                       | 1.27             | 39.52      | 1580           | 314.96             | 5647             |
| TBA          | 250 (37)   | 14.17                   | 32.87                    | 8.76             | 35.66                           | 14x14              | 0.61                       | 1.91             | 42.72      | 1982           | 342.90             | 6675             |
| TBA          | 350 (37)   | 16.79                   | 35.48                    | 8.76             | 38.28                           | 19x14              | 0.45                       | 1.91             | 45.34      | 2350           | 363.22             | 9345             |
| TBA          | 500 (37)   | 20.04                   | 38.73                    | 8.76             | 42.29                           | 27x14              | 0.32                       | 1.91             | 49.35      | 2941           | 393.70             | 13350            |

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◇ Cable marked with this symbol is a standard stock item

**Table 4 – Electrical and Engineering Data (Metric)**

| Cond. Size | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Charging Current | Dielectric Loss | Zero Sequence Impedance* | Positive Sequence Impedance* | Short Circuit Current @ 30 Cycle | Allowable Ampacity in Duct 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|----------------------|----------------------|-----------------------------|----------------------------|------------------|-----------------|--------------------------|------------------------------|----------------------------------|---------------------------------|---|
| AWG/Kcmil  | Ω/km                 | Ω/km                 | MΩ*km                       | Ω/km                       | A/km             | W/km            | Ω/1000ft                 | Ω/1000ft                     | Amp                              | Amp                             | Amp                                     |
| 1/0 (19)   | 0.5479               | 0.69                 | 0.0216                      | 0.1739                     | 0.919            | 5.6102          | 0.265 + j0.747           | 0.211 + j0.054               | 3103                             | 160                             | 195                                     |
| 2/0 (19)   | 0.4364               | 0.55                 | 0.0204                      | 0.1706                     | 0.984            | 5.9055          | 0.221 + j0.744           | 0.167 + j0.051               | 3621                             | 185                             | 220                                     |
| 4/0 (19)   | 0.2756               | 0.34                 | 0.0177                      | 0.1575                     | 1.115            | 6.8241          | 0.159 + j0.735           | 0.105 + j0.048               | 6207                             | 235                             | 280                                     |
| 250 (37)   | 0.2329               | 0.30                 | 0.0165                      | 0.1542                     | 1.214            | 7.3491          | 0.144 + j0.730           | 0.090 + j0.047               | 7242                             |                                 |   |
| 350 (37)   | 0.1640               | 0.21                 | 0.0146                      | 0.1476                     | 1.378            | 8.2677          | 0.119 + j0.723           | 0.065 + j0.045               | 9828                             | 315                             | 370                                     |
| 500 (37)   | 0.1148               | 0.15                 | 0.0128                      | 0.1378                     | 1.542            | 9.3832          | 0.100 + j0.715           | 0.046 + j0.043               | 13967                            | 380                             | 435                                     |

\*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

\*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

\*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

CN  
Calculator

